

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301040029](#)
Status: **Active**
Overview: [Specialty Lighting](#)
Description: Haztex Hazardous Location 26W with 12V Fluorescent Hand Lamp with 220V In-line Transformer 14/3 SOOW Cord Type, Cord Length 30.48m (100.0')

Documents:

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR39801

General

Product Family Portable Lighting
Series [130104](#)
Comments Class I, Division 1, Groups C and D (flammable gases and vapors); Class II, Division I, Groups F and G (ignitable dust); Class I, Zone 1, Group IIB (UL)
NEMA Configuration NEMA 5-15
Outlet None
Overview [Specialty Lighting](#)
Product Name Haztex
Type Hand Lamps, Specialty Light
UPC 78678805481

Physical

Cord Length - Primary 30.48m (100.0')
Cord Length - Secondary N/A
Depth 100.08mm (3.940")
Duty Hazardous
Guard Included Yes
Guard Type Cast Aluminum
Height 482.60mm (19.000")
Length N/A
Material - Globe Tempered Soda-Lime Glass
Material - Guard Cast Aluminum
Mounting Style Hand Held
Packaging Type Carton
Socket Construction N/A

Electrical

Bulb Type Fluorescent
Cord Type - Primary 14/3 SOOW
Lamp Type PL-C 26/41/4P
Lamp Wattage - Maximum 26W
Lumens 1800
On/Off Switch No
Voltage (Fixture) - Maximum 230VAC 50 HZ

Material Info

Engineering Number 1090-HZ12ID143P



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[130104](#) Series