





1-CONDUCTOR-FEEDTHROUGH TERMINAL BLOCK FOR FLUSH- MOUNTING PIN SPACING 5 MM / 0.197 IN 731-132 TO 731-142/048-000

ITEM-NO. (ITEM-NO.)	731-134
Cross section1 (Cross section / mm ²)	0.08 - 2.5
Cross section2 (Cross section / AWG)	28 - 14
Strip length (Strip length / mm)	8 - 9
Measured voltage (Measured voltage / V)	320
Measured shock voltage (Measured shock voltage / kV)	4
Pollution degree (Pollution degree)	2
Current intensity (Current intensity / A)	5
RM (PIN SPACING / mm)	5
P (NO. OF POLES)	4
Height (Height / mm)	12
Width (Width / mm)	35.2
Depth (Depth / mm)	15.5
No. of connection Points (No. of connection Points)	4
No. of potentials (No. of potentials)	4
COLOR (COLOR)	grau
WEIGHT (WEIGHT / g)	6.8
Comment (Comment)	L = (No. of poles x Pin Spacing) + 3 mm L1 = L + 5,8 mm L2 = L + 6,4 mm
Dimensions (Dimensions)	For thickness of mounting plate 1,5 mm max