

Double Row Terminal Blocks

Kulka® 605 GP Series

600 Volts AC/DC (Classes B/C)



605 GP 03

Specifications:

- Base, General Purpose Phenolic, 150°C (UL RTI)
- Open Back Design (Insulator Strip required for Voltage Rating - see page 112)
- JJ (GDI-30F) Material Available
- Screws, #1/4-28 Binder Head, Slotted, Brass
- Terminals, Plated Brass
- 1-6 Poles
- 1 1/8" Centers
- Wire Range With Wire Binding Screw #10 - #12 AWG – 30 Amps
- 90 Amps with Listed Wire Lugs
- UL Recognized File No. XCFR2.E47811
- CSA Certified File No. LR19766
- **CE**
- RoHS Compliant

Kulka® Catalog #	# of poles	Dimensions	
		A	B
605 GP 01 SLB	1	2.88	2.25
605 GP 02 SLB	2	4.00	3.38
605 GP 03 SLB	3	5.13	4.50
605 GP 04 SLB	4	6.25	5.63
605 GP 05 SLB	5	7.38	6.75
605 GP 06 SLB	6	8.50	7.88

mm=dim X 25.4

Hardware Options:

(Hardware options may affect ratings - consult Customer Service)

CATALOG #		PRODUCT	PAGE
MSP	KULKA	DESCRIPTION	REFERENCE
	J 605	Line to Line Jumper	See Page 107
	2502	Stud 1/4-28 Brass (.750 H)	See Page 109
		Nuts included	
PSB		Phil-Slot Brass Screw	Consult C/S

See pages 104-115 for terminal block accessories

For electronic drawings or 2D/3D CAD data, submit request at www.marathonsp.com/drawings.html

