

**Honeywell Sensing and Control**

Search

**143-303QAG-RC1 Discrete Thermistors**

(Home : Products)

**narrow your search****Products**

- Controls Monitoring and Lighting (354)
- Machine Safety (1726)
- Sensors (7016)
- Switches (9736)

**Technology**

- Control and Instrumentation (1063)
- Electromechanical (9297)
- Microstructure (2298)
- Optical/Infrared (1077)
- Thick Film (1764)
- More...



143 Series, 5,08 mm [0.2 in] disc thermistor with leads, 30,000 Ohm resistance,  $\pm 10.0\%$  tolerance, 25/85 BETA = 4261

*Actual product appearance may vary.*

**Sales & Service****Distributor Inventory****Need Help?**

Click here to contact us

**Overview**   **Specs**   **Documentation**   **Application Notes****Product Specifications**

Availability	Global
Resistance	30,000 Ohm
Tolerance	$\pm 10.0\%$
Accuracy	25 °C [77 °F]
Beta	4261
Operating Temperature	-60 °C to 125 °C [-76 °F to 257 °F]
Diameter	5,08 mm [0.20 in]
Termination Material	Tinned copper
Lead Length	38,1 mm [1.50 in]
Time Constant in Air	16.0 s
Dissipation Constant	4,0 m/W°C
Series Name	143