

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

**Part Number:** [50-57-9309](#)  
**Status:** **Active**  
**Overview:** [SL™ Modular Connectors](#)  
**Description:** 2.54mm Pitch SL™ Crimp Housing, Single Row, Version D, Back Ribs, 9 Circuits

**Documents:**

|                                                      |                                                      |
|------------------------------------------------------|------------------------------------------------------|
| <a href="#">3D Model</a>                             | <a href="#">Product Specification PS-71851 (PDF)</a> |
| <a href="#">Drawing (PDF)</a>                        | <a href="#">Test Summary TS-70058-001 (PDF)</a>      |
| <a href="#">Product Specification PS-70058 (PDF)</a> | <a href="#">RoHS Certificate of Compliance (PDF)</a> |
| <a href="#">Product Specification PS-70400 (PDF)</a> |                                                      |

**Agency Certification**

|     |           |
|-----|-----------|
| CSA | LR19980   |
| TUV | R72081037 |
| UL  | E29179    |

**General**

|                |                                        |
|----------------|----------------------------------------|
| Product Family | Crimp Housings                         |
| Series         | <a href="#">70066</a>                  |
| Application    | Signal, Wire-to-Board                  |
| Comments       | Version D                              |
| Overview       | <a href="#">SL™ Modular Connectors</a> |
| Product Name   | SL™                                    |
| UPC            | 800753578104                           |

**Physical**


|                               |                 |
|-------------------------------|-----------------|
| Circuits (maximum)            | 9               |
| Color - Resin                 | Black           |
| Flammability                  | 94V-0           |
| Gender                        | Female          |
| Glow-Wire Compliant           | No              |
| Material - Resin              | Polyester Alloy |
| Net Weight                    | 0.689/g         |
| Number of Rows                | 1               |
| Packaging Type                | Bag             |
| Panel Mount                   | No              |
| Pitch - Mating Interface      | 2.54mm          |
| Stackable                     | Yes             |
| Temperature Range - Operating | -40°C to +105°C |

**Material Info**

|                 |            |
|-----------------|------------|
| Old Part Number | 70066-0113 |
|-----------------|------------|

**Reference - Drawing Numbers**

|                       |                              |
|-----------------------|------------------------------|
| Product Specification | PS-70058, PS-70400, PS-71851 |
| Sales Drawing         | SD-70066-0106-0129           |
| Test Summary          | TS-70058-001                 |



**EU RoHS**

**ELV and RoHS  
Compliant**

**REACH SVHC**

Not Reviewed

**Low-Halogen Status**

**Not Low-Halogen**

**China RoHS**



**Need more information on product  
environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
For a multiple part number RoHS Certificate of  
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any  
non-product compliance questions.

**Search Parts in this Series**

[70066Series](#)

**Mates With**

[70004](#) Interim Clip, [70013](#) , [70022](#) , [70104](#)

**Use With**

[70021](#) , [70058](#) , [71851](#)