


Multiadapter for QFP-SMD



Stock No. RE 470

- Epoxy fibre - glass FR4 1.50 mm, double-sided 35 µm Cu
- Plated through-holes Ø 1,00 mm
- Pad spacings 0.40mm (15.7mil) and 0.50mm (19.7 mil.)
- Adaption board for 23 different SMD - QFP's

Pitch (mm)	mil.	Pin	Size (mm)
0.40	15.7	80	10 x 10
0.40	15.7	100	10 x 14
0.40	15.7	100	12 x 12
0.40	15.7	108	10 x 14
0.40	15.7	108	12 x 12
0.40	15.7	120	14 x 14
0.40	15.7	184	20 x 20
0.40	15.7	224	20 x 28
0.40	15.7	232	20 x 28
0.40	15.7	264	28 x 28
0.50	19.7	40	07 x 07
0.50	19.7	48	07 x 07
0.50	19.7	72	10 x 10
0.50	19.7	80	12 x 12
0.50	19.7	100	14 x 14
0.50	19.7	120	14 x 20
0.50	19.7	128	14 x 20
0.50	19.7	144	20 x 20
0.50	19.7	176	24 x 24
0.50	19.7	208	28 x 28
0.50	19.7	240	32 x 32
0.50	19.7	256	28 x 40
0.50	19.7	264	28 x 40

- Two component sides with chemical nickel/gold end surface and solder stop masks
- Prescratched rated break point for the separation of individual modules from the board
- Gerber data for manufacture of the solder stop masks and the soldering paste imprint will be provided free of charge on request.
- Size 123 x 203 mm