



Screw Clamp Connections


Spring Loaded



RSF 3



RSF 1



Available Options		Version	Part No.		Part No.	
Molding material		TS 32 Polyamide	0497560000			
		TS 35 Polyamide	9501160000			
		TS 32 Melamine			0270320000	
Dimensions						
Width / Length / Height mm (in.)		with TS 32		8/50/60 (.31/1.97/2.36)	11/50/60 (.43/1.97/2.36)	
Insulating stripping length		mm (in.)	12 (.47)		12 (.47)	
Technical Data						
Rated voltage / rated current / wire size		UL	600 V / 25 A / #22...12 AWG		600 V / 40 A / #14...8 AWG	
		CSA	600 V / 25 A / #22...12 AWG		300 V / 50 A / #14...8 AWG	
Terminal Rail (2 m)			Type	Part No.	Type	Part No.
		Steel	TS 32	0122800000	TS 32	0122800000
		Steel (M6 Slots)	TS 32	0676100000	TS 32	0676100000
Locking pin (1 m)—optional		Steel	SST 3	0152700000	SST 3	0152700000
End Bracket (thickness mm)						
			EWK 1 (8.5)	0206160000	EWK I (85)	0206160000
End Plate (thickness mm)						
		Polyamide	AP (3)	0270460000		
		Melamine			AP (3)	0270420000
Partition (thickness mm)						
		Polyamide	TW (1.5)	3877960000		

*To accommodate two hooked bladed crimps back-to-back per terminal, one should be located in the current bar slot, the second through the lower part of the clamp.