

TYPE AR

LED JACK .531" HEIGHT
TOP TAB & TOP LEDs, THRU HOLE
8P8C



MTJ-88ARX1-FS-LG

Also available with
panel ground tabs

TYPE AA

LED JACK .441" HEIGHT
BOTTOM TAB &
BOTTOM LEDs
THRU HOLE
8P8C



MTJ-88AAX1-FS-LG-PG




TYPE D

TOP ENTRY LED JACK .610" HEIGHT WITH LEDs NON-SHIELDED
8P8C



MTJ-88DX1-LG

LED CONFIGURATION		
SUFFIX	LED 1	LED 2
LA	YELLOW	YELLOW
LD	GREEN	GREEN
LG	YELLOW	GREEN
LH	GREEN	YELLOW
LI	ORANGE/ GREEN	ORANGE/ GREEN



Recommended PCB Layout

JACKS WITH LEDs ORDERING INFORMATION



SERIES INDICATOR
MTJ = Modular
telephone jack

8

**HOUSING
PLUG SIZE**
8 or 10

4

**NO. OF CONTACT
POSITIONS FILLED**
2, 4, 6, 8 or 10

AR

HOUSING TYPE
AR, AA, D

2

PLATING
X = Gold Flash
0 = 15 µin gold
1 = 30 µin gold
2 = 50 µin gold

1

**BODY
COLOR**
1 = Black
2 = Gray

LD

**LED
Configuration**
See Chart
above
Leave blank
for no LEDs

OPTIONS:

SMT = Surface mount tails with Hi-Temp insulator

PG = Panel Ground Tabs

LX = LED's, use LA, LD, LG, LH, LI, see LED Configuration Chart