

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION


Part Number: [0190700109](#)
Status: **Active**
Description: InsulKrimp™ Ring Tongue Terminal for 10-12 AWG Wire

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-19902-009 \(PDF\)](#)

General	
Product Family	Ring and Spade Terminals
Series	19070
Mil-Spec	N/A
Product Name	InsulKrimp™
Type	Ring
Physical	
Barrel Type	Closed
Color - Resin	Natural
Flammability	94V-2
Insulation	PVC
Material - Plating Mating	Tin
Packaging Type	Bag
Stud Size	1/2" (M12)
Wire Insulation Diameter	6.40mm (.250") max.
Wire Size AWG	10, 12
Wire Size mm²	3.30 - 5.00
Electrical	
CSA	LR18689
UL	E32244

Material Info	
Old Part Number	C-201-12X

Reference - Drawing Numbers	
Product Specification	PS-19902-009
Sales Drawing	CCD20101



Series
image - Reference only

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Halogen-Free
Status
Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[19070Series](#)

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.
Global

Description	Product #
Hand Crimp Tool	0640010100
Crimp Head for the AT-200™ Pneumatic Hand Tool	0640050100
Crimp Head for the AT-200™ Pneumatic Hand Tool	0640050300
Hand Crimp Tool	0640010300