


**558-00336**

Continuous Solid Color Vinyl Roll, 1.0" X 250', Orange, Vinyl, 250ft/RL

Article Number: 558-00336

Part Number: 558-00336

Type: HT10E250

**Base Data**

Part No.	558-00336
Type	HT10E250
Color	Orange (OG)
Features	• Continuous Vinyl Labels are made with UV stable materials for long outdoor life. • Labels are extruded in the actual color and not colored using surface inks for long term fade resistance. • Continuous Vinyl is provided in continuous rolls so that the markers can be printed and cut to any length using HellermannTyton thermal transfer printing systems.

Product Dimensions

Length (L)	250.0ft / 76.2m
Width (W) (imperial)	1.0"
Width (W)	25.4mm
Height (H)	1.0" / 25.4mm
Print Method	Thermal Transfer
Vertical Repeat	1.0" / 25.4mm
Width of Liner (WL)	1.0" / 25.4mm

Material and Specifications

Material	Vinyl
-----------------	-------

Adhesive	Acrylic / Acryl
Adhesive Operating Temperature	-40 °F to +180 °F (-40 °C to +82 °C)
Mech. Material Properties	UV resistant for 5 years outdoor exposure
Operating Temperature	-40 °F to +180 °F (-40 °C to +82 °C)
ROHS Conformity	

Logistic and Packaging

Packaging Type	roll
Pkg. Qty.	250
E-number	00 000 00
Labels per Column	1
Labels per Row	1

© HellermannTyton North America 2011 | [TS16949](#), [ISO 9001](#) and [ISO 14001 Certified](#)

7930 N. Faulkner Rd. Milwaukee, WI 53224-9517 | Fax: 800-848-9866 | Phone: 800-537-1512