



- Superior adhesive for long term reliability
- 2-up mount configuration speeds liner removal and installation
- 4-way cable tie entry makes part orientation fast and easy
- Adhesive backing allows routing of wires and cables where mounting holes cannot be drilled
- Used with *PANDUIT®* cable ties for a complete wire routing solution

‡ Cable Tie Cross Section Sizes: M = Miniature, I = Intermediate, S = Standard, HS = Heavy-Standard, LH = Light-Heavy, H = Heavy, HLM = Miniature *Tak-Ty®* Hook & Loop Cable Ties.

Part Number: ABM4H-AT-L
Product Family: 4-Way Adhesive Backed Cable Tie Mounts
Product Line: Adhesive Backed

RoHS Compliancy Status: Compliant

Part Description: 4-Way Adhesive Backed Cable Tie Mount

Product Type: Cable Tie Mounts - Adhesive Backed

Material: Nylon 6.6

Color: White

UL Recognized: E136577

Height (In.): .25

Height (mm): 6.4

Length (In.): 2.00

Length (mm): 50.8

Width (In.): 2.00

Width (mm): 50.8

Adhesive Type: Acrylic

CE Compliant: CT-ACC1 / 10.96

Environment: Indoors/High Temp

Max. Static Load (g): 907

Max. Static Load (Lbs.): 2.00

Metric Screw Size: M3

Mounting Method: Adhesive Backed

Screw Size: #6 (M3)

Std. Pkg. UOM: PK

Used With Cable Ties: M, I, S, HS, LH, H & HLM

UOM: PC

Std. Pkg. Qty.: 50

Min. Order Qty.: 50