

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

43030-0003

Status:


Active

Overview:

Micro-Fit 3.0™ Connectors

Description:

Micro-Fit 3.0™ Crimp Terminal, Female, with Select Gold (Au) Plated Phosphor Bronze Contact, 20-24 AWG, Reel



Series

image - Reference only

Documents:

- [3D Model](#)
- [Drawing \(PDF\)](#)
- [Product Specification PS-43045 \(PDF\)](#)
- [Test Summary TS-43045-002 \(PDF\)](#)
- [RoHS Certificate of Compliance \(PDF\)](#)
- [Product Literature \(PDF\)](#)

General

Product Family	Crimp Terminals
Series	43030
Application	Power
Crimp Quality Equipment	Yes
Overview	Micro-Fit 3.0™ Connectors
Packaging Alternative	43030-0009 (Loose)
Product Literature Order No	987650-5984
Product Name	Micro-Fit 3.0™
UPC	800754369169

Physical

Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Net Weight	0.062/g
Packaging Type	Reel
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.85mm max.
Wire Size AWG	20, 22, 24
Wire Size mm²	N/A

Electrical

Current - Maximum per Contact	5A
-------------------------------	----

Material Info

Reference - Drawing Numbers

Product Specification	PS-43045, RPS-43045-003, RPS-43045-004
Sales Drawing	SD-43030-****
Test Summary	TS-43045-002

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
43030Series

Mates With
43031 Micro-Fit 3.0™ Male Crimp Terminals

Use With
43025 , 43645 Micro-Fit 3.0™ Receptacle Housings, 44133 Micro-Fit BMI™ Panel Mount Receptacle Housings

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Hand Crimp Tool	0638190000
FineAdjust™	0639004500
Applicator for Insulation OD	

1.30-1.85mm - 20-24 AWG T2 Terminator™ for insulation OD	<u>0639104500</u>
1.30-1.85mm - 20-24 AWG Insertion Tool for Crimp Terminal	<u>0638120800</u>
FineAdjust™ Applicator for Insulation OD	<u>0639018800</u>
1.10-1.30mm - 20-24 AWG FineAdjust™ Applicator for Insulation OD	<u>0639018900</u>
0.91-1.09mm - 20-24 AWG T2 Terminator™ for insulation OD	<u>0639118800</u>
1.10-1.30mm - 20-24 AWG T2 Terminator™ for insulation OD	<u>0639118900</u>
0.91-1.09mm - 20-24 AWG Extraction Tool	<u>0011030043</u>
Japan	
Description	Product #
Applicator for M211A Bench Press, 20-30 AWG Wire	<u>0572983000</u>

This document was generated on 10/14/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[43030-0003](#) [43030-0003 \(Cut Strip\)](#) [43030-0003 \(Mouser Reel\)](#)