

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0875200011

Status:

Inactive

Description:

3-in-1 Combo Connector<br>Wide SCSI/2.00mm/Power, Reverse Face, Right Angle, 4|68|12 Circuits

Documents:

General

|                |                            |
|----------------|----------------------------|
| Product Family | I/O Connectors             |
| Series         | 87520                      |
| Application    | Wire-to-Board              |
| Comments       | Reverse Face/ Bottom Mount |
| Component Type | Plug, Receptacle           |
| Product Name   | 3-in-1 Combo, SCSI+        |
| Type           | N/A                        |

Physical

|                                |                                                |
|--------------------------------|------------------------------------------------|
| Circuits (Loaded)              | 84                                             |
| Circuits (maximum)             | 84                                             |
| Durability (mating cycles max) | 100                                            |
| Lock to Mating Part            | None                                           |
| Material - Plating Mating      | Gold                                           |
| Orientation                    | Right Angle                                    |
| PCB Retention                  | Yes                                            |
| PCB Thickness - Recommended    | 1.00mm (.039")                                 |
| Packaging Type                 | Tray                                           |
| Panel Mount                    | No                                             |
| Pitch - Mating Interface       | 1.27mm (.050"), 2.00mm (.079"), 5.00mm (.197") |
| Plating min - Mating           | 0.762µm (30µ")                                 |
| Polarized to Mating Part       | Yes                                            |
| Surface Mount Compatible (SMC) | Yes                                            |
| Temperature Range - Operating  | -40°C to +105°C                                |
| Termination Interface: Style   | Through Hole                                   |
| Wire Size AWG                  | N/A                                            |

Electrical

|                               |        |
|-------------------------------|--------|
| Current - Maximum per Contact | 1A, 5A |
| Shielded                      | Yes    |
| Voltage - Maximum             | 12V    |

Material Info

EU RoHS

China RoHS

Compliance Status

Not Reviewed

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

Need more information on product environmental compliance?

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)

For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

87520Series

Mates With

2mm receptacle, [Link:70498-4068](#) , [Link:8981](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION