


LOC	DIST	P	F	ZONE	LTR	DESCRIPTION	DATE	APPD
CE	16				E	REV PER 0A00-0406-95	11-1-95	DDE



1. DIMENSIONS IN [] ARE IN INCHES.
2. INSTRUCTION SHEET 6935.
- 3

BODY: BRASS
CAPILLARY: CERAMIC
COUPLING NUT: ZINC
STRAIN RELIEF: TPE
- 4

BODY: ELECTROLESS NICKEL
COUPLING NUT: ELECTROLESS NICKEL
- 5

USE WITH 900µm BUFFERED FIBER ONLY.

METRIC

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm TOLERANCES ON : 2 PLC DEC ± — 3 PLC DEC ± — ANGLES ± —	DR 2-1-91 R.HILEMAN CHK 2-1-91 B.BRIGGS APPD 2-7-91 F.ANTONICELLI APPD 2-7-91 D.COLLINS PRODUCT SPEC 108-45113	NAME CONNECTOR KIT, RIGHT ANGLE, 2.5mm BAYONET, OPTIMATE®
FINISH	APPLICATION SPEC	SIZE C
	WEIGHT	FSCM NO 00779
		DRAWING NO 502674
		SCALE 2:1
		SHEET 1 OF 1

OBSOLETE

BLACK

GREEN

140±3 µm

502674-2

BLACK

—

125±2 µm

502674-1

STRAIN RELIEF
COLORS

COLOR DOT

FIBER SIZE

PART NO

AMP

AMP INCORPORATED
Harrisburg, Pa. 17105