

KGM

Locknuts



Type KGM: Standard nut, plastic



Type KGM: SUB-D9, PB, SUB-D25




Type GMT: Split locknut

Product description

Hexagonal nut with metric threads for attaching components together.

For routing SUB-D, DVI or PROFIBUS connectors in combination with the split cable glands KVT, special locknuts with cut-outs are required.



Specification

Material	Polyamid (PA) / Polycarbonate (PC) / Brass (BR), nickel-plated
Colour	■ grey (similar RAL 7035) ■ black ■ Brass
Flame class	UL94-Vo, self-extinguishing
Temperature	- 30°C to + 120°C
Properties	Halogen-free, silicone-free

Accessories

KVT, KVT-SNAP, KVT-W90	
Split cable glands	Page 22 - 26
QVT Split cable glands	Page 42
KEL-DPZ Cable entry plates	Page 56 - 57
KEL-DPF Cable entry inserts	Page 61

Thread	Type	Order No.	Material	Height [mm]	Wrench size	Diagonal [mm]	Cut-out a×b[mm]	PU
--------	------	-----------	----------	-------------	-------------	---------------	-----------------	----

Type KGM: Standard nut, plastic

M20 × 1.5	KGM 20	■ 52273 ■ 52283	PA	7.0	SW 26	28.2	-	10
M25 × 1.5	KGM 25	■ 52274 ■ 52284	PA	7.0	SW 32	36	-	10
M32 × 1.5	KGM 32	■ 52275 ■ 52285	PA	7.0	SW 41	46	-	10
M40 × 1.5	KGM 40	■ 52276 ■ 52286	PA	7.0	SW 50	56	-	10
M50 × 1.5	KGM 50	■ 52277 ■ 52287	PA	8.6	SW 60	66	-	10
M63 × 1.5	KGM 63	■ 52278 ■ 52288	PA	8.6	SW 75	83	-	5
M63 × 1.5	GM 63	■ 56152	BR	5.5	SW 70	78	-	5

Type KGM: PB, SUB-D9, SUB-D25

M32 × 1.5	KGM-SUB-D9	■ 45105 ■ 45106	PC	7.0	SW 41	46	35 × 16	10
M40 × 1.5	KGM-PB	■ 45107 ■ 45109	PC	8.0	SW 50	55	43 × 17	10
M50 × 1.5	KGM-SUB-D25	■ 45108 ■ 45110	PC	8.0	SW 60	66	55 × 16	10

Type GMT: Split locknut

M20 × 1.5	GMT 20	■ 31110	PA	9.0	SW 27	29	-	10
M25 × 1.5	GMT 25	■ 31100	PA	9.0	SW 32	35	-	10
M32 × 1.5	GMT 32	■ 31120	PA	12.0	SW 40	44	-	10
M50 × 1.5	GMT 50	■ 31140	PA	15.0	SW 63	69	-	10