

Search Results

Evaluate

- Brochures
- PDF-High Speed D ..
- FAQ's

Design a Solution

- Catalog Cut Sheet
- PDF-F1RBZN-9608- ..
- Part Drawings
- PDF-QuickNet HDQ ..
- Specification Sheets
- PDF-QuickNet Cas ..
- PDF-QuickNet HDQ ..

How to Buy

- Bill of Material
- Favorite Products List
- Locate Distributor

Install & Maintain

- Installation Instructions
- PDF-Installation ..

Home > Product On-Line Catalog > Search Results >

Current refinements (click  to remove) [Search Tips](#) 

 **Text Search: 'F1RBZN-9608-10F'**

Your search criteria matched only one product, shown below

F1RBZN-9608-10F



Quicknet™ HDQ Series High Density Fiber Optic Cassettes:

- Mounts to standard 19" rack rails
- Low insertion loss of 0.5dB max, per optimized cassette and 0.75dB max. per standard cassette; ensures system meets IEEE 802.3ae max. channel loss specification of < 2.6dB
- Return loss: ≥ 26dB
- Adapter housing colors follow TIA/EIA - 568-C.3 suggested color identification scheme
- Connect together with high-density female MTP* cable assemblies as interconnection network
- Significantly reduce installation time and labor by eliminating field connector termination
- Factory terminated, assembled, and 100% tested
- Insertion loss data provided on every fiber cassette
- Lifetime traceability of test data to a Q.C. number
- 10Gig OM3 50/125um fiber cassettes are tested per IEEE 802.3ae 10 GbE to support network transmission speeds up to 10 Gb/s for link lengths up to 300 meters and up to 550 meters for OM4 at 850 nm; backward compatible with all 50/125um (OM2) MPO or MTP system

requirements

Quicknet™ Cassette Rear Cable Manager:

- Mounts horizontally to standard 19" rack rails
- Fiber Management Slack Spools can be used to manage MTP Interconnect Cable

▪ Part Number	F1RBZN-9608-10F
▪ RoHS Compliancy Status	Compliant
▪ Note	Intended for use in fixed installations which are outside the scope of RoHS
▪ Part Description	QuickNet™ HDQ Series High Density Fiber Optic Cassette; 1RU 96-fiber B-type labeling; 10Gb OM4 8-fiber MTP to LC Pre-terminated – flipped polarity.
▪ Pricing Description	8 Fiber High Density OM4 10GbE MTP To LC Cassette - B-type labeling
▪ Min. Order UOM	PC
▪ Min. Order Qty.	1
▪ BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
▪ Add to Favorite Product List	<input type="checkbox"/>

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.