



Search Results

- Evaluate
  - FAQ's
- Design a Solution
  - Specification Sheets
  - PDF-24x4 FiberRu ..
- How to Buy
  - Bill of Material
  - Favorite Products List
  - Locate Distributor
- Install & Maintain
  - Installation Instructions
  - PDF-FiberRunner ..

Home > Product On-Line Catalog > Search Results >

Current refinements (click  to remove) Search Tips [?](#)

Text Search: 'FRIV4524X4BL'

Your search criteria matched only one product, shown below

**FRIV4524X4BL**



The complete selection of fittings feature bend radius control to prevent excessive bends in high performance copper and fiber optic cabling.

- Minimum 3" (76.2mm) bend radius control fittings
- Protect against signal loss and performance degradation
- Assemble using FRBC QuikLock™ couplers
- For other standard colors replace suffix YL (Yellow) with OR (Orange) or BL (Black)

▪ Part Number	FRIV4524X4BL
▪ RoHS Compliancy Status	Compliant
▪ Product Name	24x4 Inside Vertical 45° Fitting and Cover
▪ Part Description	Attaches to 24x4 channel and/or fittings to create a 45° upward angle from a straight horizontal run. Used with outside vertical 45° angle fitting FROV4524X4BL to change level of a straight horizontal run. Includes cover.
▪ Material	ABS
▪ Color	Black
▪ Fitting Type	Inside Vertical 45°
▪ Couplers Required	(2 pcs.) FRBC24X4BL
▪ System Type	24 x 4 FiberRunner Fitting
▪ System Size	24x4
▪ CE Compliant	No
▪ Pricing Description	Fitting and Cover, Inside Vertical 45o, 24x4 (600mm x 100mm) FiberRunner, BL
▪ Min. Order UOM	PC
▪ Min. Order Qty.	1
▪ BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
▪ Add to Favorite Product List	<input type="checkbox"/>

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.