




DIN 965 A

~ISO 7046-1

4.8

Standard withdrawn



BN 3333

Pozi flat countersunk head machine screws

form Z

Steel 4.8

zinc plated blue

- ~UNI 7688
- ~ČSN 021152



All lengths fully threaded
Countersink must be designed according to the corresponding standard!

Article#	d ₁	d ₂ max.	k max.		m~	t min.	t max.	L
1536818	M2	3,8	1,2	1	2,2	0,92	1,17	4
1536826								5
1536834								6
1536842								8
1536850								10
1536869								12
2097028								16
2097036								20
2097044	M2,5	4,7	1,5	1	2,5	1,22	1,47	4
1536877								5
1536885								6
1536893								8
1536907								10
1536915								12
2097052								16
2097060								20
2097079	M3	5,6	1,65	1	2,8	1,48	1,73	4
1536923								5
1536931								6
1536958								8
1536966								10
1536974								12
1536982								16
1536990								20
1537008								25
1537016								30

Article#	d ₁	d ₂ max.	k max.		m~	t min.	t max.	L
2097087	M3	5,6	1,65	1	2,8	1,48	1,73	35
2097095								40
2097109								50
2097117	(M3,5)	6,5	1,93	2	3,7	1,34	1,8	6
2097125								8
2097133								10
2097141								12
2097168								16
2097176								20
3646080	M4	7,5	2,2	2	4	1,6	2,06	5
1537024								6
1537032								8
1537040								10
1537059								12
1537067								16
1537075								20
1537083								25
1537091								30
1537105								35
1537113								40
5402888								45
2097184								50
2097192								60
2097206	M5	9,2	2,5	2	4,4	2,05	2,51	6
1537121								8
1537148								10
1537156								12
1537164								16
1537172								20
1537180								25
1537199								30
1537202								35
1537210								40
5402889								45
1537229								50
5402890								60
5402891								70
1537237	M6	11	3	3	6,1	2,46	2,92	10
1537245								12
1537253								16
1537261								20

Article#	d ₁	d ₂ max.	k max.		m~	t min.	t max.	L
1537288	M6	11	3	3	6,1	2,46	2,92	25
1537296								30
1537318								35
1538403								40
5402892								45
1538411								50
5402893								60
5402894								70
5402895	M8	14,5	4	4	8,5	3,86	4,32	16
5402896								20
5402897								25
5402898								30
5402899								40
5402900								50