


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0190710150
Status: Active
Description: InsulKrimp™ Ring Tongue Terminal for 8 AWG Wire

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-19902-009 \(PDF\)](#)

General	
Product Family	Ring and Spade Terminals
Series	19071
Mil-Spec	N/A
Product Name	InsulKrimp™
Type	Ring
Physical	
Barrel Type	Closed
Color - Resin	Natural
Insulation	PVC
Material - Plating Mating	Tin
Packaging Type	Bag
Stud Size	3/8" (M9)
Wire Insulation Diameter	6.70mm (.265") max.
Wire Size AWG	8
Material Info	
Old Part Number	D-651-38X
Reference - Drawing Numbers	
Product Specification	PS-19902-009
Sales Drawing	SD-19071-002



Series image - Reference only

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Halogen-Free
Status
Not Reviewed

China RoHS

Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
19071Series

Application Tooling FAQ <i>Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.</i> Global	
Description	Product #
Putt Pump Dieless Head System	0192860065
Die Set (large) for the HHLS Hydraulic Crimper	0192890001
Manual Putt Pump Hydraulic System, Die set required	0192860117

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION