



CDP101B Drill Press



Part no. 6505510

A precision manufactured pillar drill for the general workshop. This latest design builds on the success of previous models offering a comprehensive specification, dependable operation and improved safety. Multi speed adjustment means the CDP101B is ideal for drilling metal, wood and plastic.

- Chuck capacity 13mm (Spindle taper JT33)
- 5 speeds from 500 - 2500 RPM
- 245 Watt, 230v / 1 phase electric motor (Totally Enclosed Fan Cooled)
- Safety features include electrical cut-out on belt guard, combined NVR / stop start switch and clear perspex chuck guard.
- Also has dry type tilting work table 165 x 160mm, depth gauge, user reference chart and fitted BS plug.
- Dimensions - chuck to column 102mm (horizontal), chuck to table 182mm max (vertical).
- Overall height 570mm