




Drawings not to scale
All dimensions in mm

SPECIFICATION

SWITCHING DISTANCE	Min. mm	8.0
OPERATING TEMPERATURE	Deg. °C	-20° + 85°
STORAGE TEMPERATURE	Deg. °C	-25° + 85°
CASE MATERIAL		Brass-nickel plated

METAL THREADED MAGNET

PART NUMBER
PTM 12

Rev. No.	Revision Note	Date	Signature
B	WEB SITE	1-10-98	RG

As part of the company policy of continued product improvement, specifications may change without notice. Our sales office will be pleased to help you with the latest information on this product range and details of our full design and manufacturing service. All products are supplied to our standard conditions of sale otherwise agreed in writing.



BS5750/ISO 9000
Reg. No. FM 21080