


FIBOX

WINDOWS

FIBOX WINDOWS







Simple to mount.
Self-extinguishing,
impact resistant polycarbonate.







FIBOX SOLID FRAME



FIBOX Inspection Windows permit both viewing and access to readouts and controls which are surface mounted on plastic or metal enclosures. While providing access, when cover closed, these inspection windows maintain enclosure environmental ratings up to NEMA 4. Four new second generation windows L12 II, L24 II, L43 II and L44 II, feature transparent smoked gray polycarbonate with textured sides and stylish design.

FIBOX INSPECTION WINDOWS	Remarks	IP	Size inch.	ORDER SYMBOL	Size mm
L44 II 	For 36 modules (1 module = 17,5 mm) (1 module = 0,69 inch.)  Smoked transparent cover	65	14.9 x 13.0	L44 II	377 x 331
L43 II 	For 26 modules  Smoked transparent cover	65	13.0 x 10.9	L43 II	331 x 277
L24 II 	For 24 modules High cover  Smoked transparent cover	65	9.8 x 8.6	L24 II	248 x 218
L12 II Pat.Reg. 383990 	For 12 modules High cover  Smoked transparent cover	65	9.8 x 5.0	L12 II	248 x 128
FRONT PLATES FOR WINDOWS L12, L 24, L12 II and L24 II 	12 modules 2 x 12 modules			B12 10621-45 B24 10620-45	

FIBOX INSPECTION WINDOWS	Remarks	IP	Size inch.	ORDER SYMBOL	Size mm																																			
L24	For 24 modules Low clear cover	65	9.8 x 8.6	L24	248 x 218																																			
L12	For 12 modules Low clear cover	65	9.8 x 5.0	L12	248 x 128																																			
L13	For 13 modules Clear cover	65	10.1 x 4.3	L13	257 x 108																																			
L02-L10 <table><tr><th>TYPE</th><th colspan="2">A</th><th colspan="2">B</th></tr><tr><th></th><th>mm</th><th>in.</th><th>mm</th><th>in.</th></tr><tr><td>L02</td><td>59</td><td>2.3</td><td>44</td><td>1.7</td></tr><tr><td>L04</td><td>94.5</td><td>3.7</td><td>78</td><td>3.1</td></tr><tr><td>L06</td><td>129.5</td><td>5.1</td><td>114</td><td>4.5</td></tr><tr><td>L08</td><td>163</td><td>6.4</td><td>146</td><td>5.7</td></tr><tr><td>L10</td><td>200</td><td>7.9</td><td>183</td><td>7.2</td></tr></table>	TYPE	A		B			mm	in.	mm	in.	L02	59	2.3	44	1.7	L04	94.5	3.7	78	3.1	L06	129.5	5.1	114	4.5	L08	163	6.4	146	5.7	L10	200	7.9	183	7.2	For 10 modules For 8 modules For 6 modules For 4 modules For 2 modules Clear cover	54 54 54 54 54	7.8 x 3.0 6.4 x 3.0 5.1 x 3.0 3.8 x 3.0 2.4 x 3.0	L10 L08 L06 L04 L02	199 x 77 162 x 77 130 x 77 96 x 77 60 x 77
TYPE	A		B																																					
	mm	in.	mm	in.																																				
L02	59	2.3	44	1.7																																				
L04	94.5	3.7	78	3.1																																				
L06	129.5	5.1	114	4.5																																				
L08	163	6.4	146	5.7																																				
L10	200	7.9	183	7.2																																				

FIBOX SOLID FRAMES	Remarks		ORDER SYMBOL	Size inch/ Size mm
 	Frame, with opening Smoked transparent cover		Cover 28/28-0	11 x 11 280 x 280
	Frame, no opening Smoked transparent cover		Cover 28/28-D	11 x 11 280 x 280
 	Frame with one DIN opening Smoked transparent cover		SF PC2828-SG-12-1	11 x 11 x 2.1 280 x 280 x 54
	Frame with two DIN openings Smoked transparent cover		SF PC2828-SG-12-2	11 x 11 x 2.1 280 x 280 x 54

Data subject to change without notice.


FEATURES YOU'VE NEVER SEEN BEFORE

- Ingress protection NEMA 4, 12
IP 54-IP 65
- Temperature range - 40°F to +248°F / - 40°C – +120°C
- Chemical resistance to concentrated mineral acids, organic acid, oxidants, deducing agents, neutral /acid salt solutions, grease & oil
 - Resistance to U.V. radiation
 - Self-extinguishing to UL94
 - Non-hygroscopic

Data subject to change without notice.

CUSTOMIZATION

Enclosures can be machined, painted, screen printed and preassembled to meet your customization requirements. Fibox's service center offers complete CNC machining, hinge mounting, screen printing, assembly and much more. Our wide selection of enclosures and accessories can be customized to create a unique enclosure meeting your application requirements.





INSTRUMENT PROTECTION WINDOWS

Instrument Protection Windows (IPW's) provide NEMA 4X protection for front panel mounted meters, instruments and operator interface stations, while still permitting access. IPW's are available in 4 sizes. These protection window kits can be factory or field installed and can protect both low and high profile instruments. All polyurethane gaskets are foamed in place for hassle free mounting in a simply drilled pattern of 4 small holes. IPW's are available from stock and are suitable for use with metal and non-metallic enclosures.

ORDER SYMBOL

SIZE

IPW 2819	11 x 7.5 (hinged on 11" side)
IPW 1928	11 x 7.5 (hinged on 7.5" side)
IPW 2828	11 x 11
IPW 3819	15 x 7.5
IPW 3828	15 x 11

NEW

Usable depth is 2.8". Custom depths are available



FIBOX INC.
Phone: 888.342.6987

810 Cromwell Park Drive, Suite R
www.fiboxusa.com

Glen Burnie, MD 21061
Fax: 410.760.8686