


DH-25CM
CONTACTOR-3PST, NO
120AMP., 400Hz, 28 VDC COIL

REVISIONS

REV.	ECO	DESCRIPTION	DATE	APPROVED
P	34653	(REF) ADDED TO CONNECTOR	06JAN1998	RSS



ALL DIMENSIONS ARE IN INCHES



TE CONNECTIVITY
175 N. DIAMOND STREET MANSFIELD,
OHIO 44902

TITLE

CONTACTOR-3PST, NO
120AMP., 400Hz, 28 VDC COIL

TE P.N.

1616017-3

DWG NO.

DH-25CM

DS DATA SHEET

CAGE CODE
74063

SCALE
NONE


SHEET
1 OF 2

REV
P

GENERAL SPECIFICATION

CONSTRUCTION	HERMETICALLY SEALED
CONTACTS	
NOMINAL CONTACT VOLTAGE	115/200 VAC, 400 HZ
MAIN CONTACT CONFIGURATION	3PST NO
RATING: RESISTIVE	120 AMP, 400 HZ
INDUCTIVE	120 AMP, 400 HZ
AUXILIARY CONTACT CONFIGURATION	7PST, 3 N.O. - 4 N.C
RATING	7.5 AMP, 400 HZ
NOMINAL COIL VOLTAGE	28 VDC
PICKUP VOLTAGE	21 VDC MAX. AT 120°C
	18 VDC MAX. AT 71°C
DROPOUT VOLTAGE	7 +0, -5.5 VDC
TEMPERATURE RANGE	-55°C TO +120°C
MIN. OPERATING CYCLES	50,000
MAX. WEIGHT	2 LBS. 6 OZ.

SCHEMATIC



TE CONNECTIVITY
175 N. DIAMOND STREET MANSFIELD,
OHIO 44902

TITLE

CONTACTOR-3PST, NO
120AMP., 400Hz, 28 VDC COIL

TE P.N.

1616017-3

DWG NO.

DH-25CM

DS

DATA SHEET

CAGE CODE
74063

SCALE
NONE

SHEET
2 OF 2

REV
P