





© COPYRIGHT



SECTION A-A



POINT OF MEASUREMENT



SECTION B-B

- 1 PLATED WITH .000030 [0.00076] GOLD, OVER .000050 [0.00127] NICKEL UNDERPLATE.
- 2 PLATED INTERNALLY WITH .000030 [0.00076] GOLD.
- 3 INSULATION RANGE: .060-.130 [1.52 - 3.30] OUTSIDE DIAMETER.

REVISIONS				
P	F	ZONE	LTR	DESCRIPTION
		Z		REVISED PER ECR-12-013323
		Z1		REVISED PER ECR-14-005682
				DATE
				APPROVED
				10AUG12 TM
				18APR14 KD

350547-7	MINI	GOLD	1	.012 [0.30] BRASS	350218-7
350547-6				.012 [0.30] PH. BRZ	350218-6
350547-3	MINI	PRE-TIN	2	.012 [0.30] PH. BRZ	350218-3
350547-2		GOLD		.012 [0.30]	350218-2
350547-1		PRE-TIN		BRASS	350218-1
LOOSE PIECE (REF)	APPLICATOR TYPE	FINISH		MATERIAL	PART NO

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES (MM) TOLERANCES ON DECIMALS ±.015 [38] ANGLES ±

WIRE RANGE
20-14 AWG

INSULATION RANGE



CONTRACT NO

DR M. FEHER 5-6-81

CHK S. Heide 6/9/81

APPD Dr. Polerub 6-10-81

APPD

DSGN APPD

OTHER APPD



TE Connectivity

NAME PIN,
UNIVERSAL MATE-N-LOK

SIZE B CODE IDENT NO 00779 DRAWING NO 350218

SCALE 4-1 SHEET

CUSTOMER DRAWING