


PFB 92 x 92 x 38 MM SERIES


DIMENSIONS DRAWING



UNIT: $\frac{\text{mm}}{(\text{INCH})}$


P & Q CURVE (AT RATED VOLTAGE)

MOUNTING PANEL CUTOUT



OUTLET SIDE

INLET SIDE



UNIT: $\frac{\text{mm}}{(\text{INCH})}$

- * Bearing Type: Ball Bearings
- * Material: Plastic (UL94V-0)
- * Impeller & Frame: Plastic (UL94V-0)
- * Lead Wires: UL 1007 AWG#24 OR Equivalent
- * Red Wire Positive (+)
- * Black Wire Negative (-)
- * Weight: 250g (8.82 oz)

MODEL		Rated Voltage	Operating Voltage Range	Rated Current	Rated Input Power	Speed	Maximum Air Flow		Maximum Air Pressure		Noise
PART NO.	FUNCTION	VDC	VDC	Amp	Watt	R.P.M.	m³ /min	CFM	mmH₂O	IN H₂O	dB-A
PFB0912HHE	-R00 / -F00	12	7.0 to 13.2	0.33	3.96	3200	1.933	68.26	7.76	0.305	43.5
PFB0912VHE	-R00 / -F00	12	7.0 to 13.2	0.38	4.56	3800	2.287	80.77	10.88	0.428	46.2
PFB0912SHE	-R00 / -F00	12	7.0 to 13.2	0.55	6.60	4400	2.668	94.22	14.67	0.578	51.7
PFB0912EHE	-R00 / -F00	12	7.0 to 13.2	0.68	8.16	4800	2.936	103.67	17.56	0.691	54.0
PFB0924EHE	-R00 / -F00	24	14.0 to 26.4	0.33	7.92						
PFB0948EHE	-R00 / -F00	48	28.0 to 56.0	0.21	10.08						
PFB0912GHE	-R00 / -F00	12	7.0 to 13.2	1.22	14.64	6000	3.662	129.31	25.78	1.015	60.5
PFB0924GHE	-R00 / -F00	24	14.0 to 26.4	0.63	15.12						
PFB0948GHE	-R00 / -F00	48	28.0 to 56.0	0.36	16.80						
PFB0912UHE	-R00 / -F00	12	7.0 to 13.2	1.96	23.52	7000	4.347	153.52	36.79	1.449	64.0
PFB0924UHE	-R00 / -F00	24	14.0 to 26.4	1.02	24.48						
PFB0948UHE	-R00 / -F00	48	28.0 to 56.0	0.60	28.80						
PFB0912DHE	-R00 / -F00	12	7.0 to 13.2	3.10	37.20	8000	4.957	175.03	46.21	1.819	66.5
PFB0924DHE	-R00 / -F00	24	14.0 to 26.4	1.45	34.80						

- * Function type is optional.
- * The max. air flow and the speed are measured in free air ; max. air pressure is measured at zero air flow.
- * Noise is measured in anechoic chamber in free air, one meter from intake side.
- * All readings are typical values at rated voltage.
- * Specifications are subject to change without notice.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Delta Electronics:

[PFB0948GHE-F00](#) [PFB0948EHE](#) [PFB0912VHE-R00](#) [PFB0912VHE-F00](#) [PFB0948UHE-R00](#) [PFB0912VHE](#)
[PFB0912EHE-F00](#) [PFB0912EHE-R00](#) [PFB0948UHE](#) [PFB0948EHE-R00](#) [PFB0924EHE-R00](#) [PFB0924GHE-R00](#)
[PFB0924GHE-F00](#) [PFB0912SHE-F00](#) [PFB0924UHE](#) [PFB0912SHE-R00](#) [PFB0948GHE-R00](#) [PFB0924UHE-F00](#)
[PFB0924EHE-F00](#) [PFB0912EHE](#) [PFB0912UHE-F00](#) [PFB0924DHE-F00](#) [PFB0948EHE-F00](#) [PFB0912HHE-R00](#)
[PFB0924UHE-R00](#) [PFB0924DHE-R00](#) [PFB0912HHE](#) [PFB0912SHE](#) [PFB0912UHE](#) [PFB0912GHE-R00](#)
[PFB0912HHE-F00](#) [PFB0912DHE-R00](#) [PFB0924GHE](#) [PFB0948UHE-F00](#) [PFB0912GHE-F00](#) [PFB0924DHE](#)
[PFB0948UHE-TP16](#) [PFB0912GHE](#) [PFB0924EHE](#) [PFB0912UHE-R00](#) [PFB0948GHE](#)