




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			P	REV PER ECO 12-022506	1-22-13	CT	WB



.145-.151 [3.68-3.84]	NIC66E11A18AA0	1-208599-6
.145-.151 [3.68-3.84]	NIC66E11A00AA1	1-208599-5
.145-.151 [3.68-3.84]	-	1-208599-4
.145-.151 [3.68-3.84]	NIC66E11A12AAD	1-208599-3
#4-40 CLINCH NUTS	-	1-208599-2
.145-.151 [3.68-3.84]	NIC66E11A00AA0	1-208599-1
.145-.151 [3.68-3.84]	NIC66E11A11AA0	1-208599-0
.145-.151 [3.68-3.84]	NIC66E11A16AA0	208599-9
.145-.151 [3.68-3.84]	NIC66E11A23AA0	208599-8
.145-.151 [3.68-3.84]	NIC66E11A03AA1	208599-7
.145-.151 [3.68-3.84]	NIC66E11A50AA0	208599-6
.145-.151 [3.68-3.84]	NIC66E11A22AA1	208599-5
#6-32 CLINCH NUTS	NIC66E11A12CB0	208599-4
#6-32 CLINCH NUTS	NIC66E11A19CB1	208599-3
.145-.151 [3.68-3.84]	NIC66E11A01AA1	208599-2
.145-.151 [3.68-3.84]	NIC66E11A01AA0	208599-1
DIM A	DESCRIPTIVE NUMBER	PART NUMBER

1. CONTACTS ARE SHOWN IN POSITION FOR ILLUSTRATION ONLY. FOR SHIPMENT CONTACTS ARE INCLUDED IN A CONTAINER WITHIN THE CONNECTOR PACKAGE. COAX CONTACTS ARE NOT SUPPLIED AND MUST BE ORDERED SEPARATELY.
2. ALL CONTACT CAVITIES IN MODULES A & B ARE LOCATED WITHIN .006 [0.15] DIA TRUE POSITION. ALL CONTACT CAVITIES IN MODULE C ARE LOCATED WITHIN .020 [0.51] DIA TRUE POSITION.
3. POLARIZING KEYS SHOWN IN POSITION 01 FOR ILLUSTRATION ONLY. CONNECTORS SHIPPED WITH KEYING PER ORDERING INSTRUCTIONS. CONTACT INSERTS AS SHOWN FOR ILLUSTRATION ONLY. SEE TABLE FOR DISSCRIPTIVE NUMBER.

THIS DRAWING IS A CONTROLLED DOCUMENT.						OWN C.C.THOMAS		11-20-95	
DIMENSIONS: INCHES						TOLERANCES UNLESS OTHERWISE SPECIFIED:		QIR R.GROSS	
								4-11-96	
						APVD R.GROSS		NAME	
						PRODUCT SPEC			
APPLICATION SPEC						RECEPTACLE ASSY,SIZE 1,ARINC 600			
MATERIAL SEE CALLOUTS						FINISH		SIZE	
								CAGE CODE	
WEIGHT						DRAWING NO		RESTRICTED TO	
CUSTOMER DRAWING						A1 00779		C=208599	
SCALE						1:1		SHEET	
REV						P		OF	