



	Bore d mm	Outside diameter D mm	Dimensions mm						Rated Loads		Hub Pressure N/cm ²	Nut Torque Nm	Approx. Weight kg
RS Article no.			L	L1	A1	A2	B	B1	Torque Nm	Thrust kN			
7785001	15	38	38	19	32	38	8	8	181	13.4	7650	140	0.235
7785004	16	38							197	14.6			
7785008	17	38							231	16.4			
7785017	18	38							266	18.0			
7785010	19	38							282	19.6			
7785014	20	45	47.5	21.5	38	44.5	11	9.5	290	21.0	6500	170	0.320
7785023	22	45							316	24.0			
7785026	24	45							380	27.0			
7785020	25	45							392	29.0			