

[Home](#) > [Products](#) > > [V923](#) > [V923YLF](#)

You may also like...

V923YLF

Category:
Generic Part: V923

Market Group: VIDEO

Description: HDMI DUAL PORT RECEIVER

Parameters

Speed	NA
Temperature	C
Voltage	1.8 V
Status	Active
Sample	Yes
Minimum Order Quantity	60
Factory Order Increment	60

Distributor Inventory

No Pricing information is available from our Distributors at this time.

Documents

No documents available for this part at this time.

Package

Package	TQFP 144 (EGG144)
Description	TQFP 20 X 20 X 1.0 MM EXPOSED PAD
Status	Active
Class	PLASTIC
Category	Green
Pb (Lead) Free	Yes
Mark	Y
Package Type	TQFP
Lead Count	144
Length	20.0 mm
Width	20.0 mm
Thickness	1.0 mm
Pitch	0.5 mm
Tube / Tray	TRAY
Quantity per Tube/Tray	60
Quantity per Reel	500
Moisture Sensitivity Level (MSL)	3
Moisture Exposure Floor Life	168hrs@<30C/60%RH
Peak Reflow Temperature	260Â°C
Rebake Conditions	48hrs@125C
Related Package Documents	view documents