


Helagaine Braided Sleeving

- Helagaine is a range of expandable braided sleeving
- Offers a simple method of protecting cables, hoses and wire bundles
- Lightweight woven sleeving, available in three materials
- Covers a wide range of cable diameters
- Helagaine can also be used for cosmetic purposes making very neat and aesthetically pleasing wire looms
- Use HSG0 hot cutting tool to prevent fraying



Polyester Braided Sleeving

Name	Helagaine
Material	Polyester
Min Working Temperature	-50°C
Max. Working Temperature	150°C
Intermittent Temperature	220°C
Flammability	V2
Halogen Content	Halogen Free
Standard Colours	Black (BK) or Grey (GY)

Polyester Braided Sleeving

Reference	Min ID	Max ID	Coil Length
HEGP05(BK) / HEGP05(GY)	3.0	9.0	100m
HEGP10(BK) / HEGP10(GY)	7.0	15.0	100m
HEGP15(BK) / HEGP15(GY)	10.0	20.0	100m
HEGP20(BK) / HEGP20(GY)	14.0	26.0	50m
HEGP25(BK) / HEGP25(GY)	18.0	34.0	50m
HEGP30(BK) / HEGP30(GY)	20.0	40.0	50m

All dimensions are in mm (nominal) and are subject to technical modification.
Note: Short coils available to special order.

Polyester VO Braided Sleeving

Name	Helagaine
Material	Polyester VO
Min Working Temperature	-50°C
Max. Working Temperature	150°C
Intermittent Temperature	220°C
Flammability	VO
Standard Colours	Grey with Black Thread

Polyester VO Braided Sleeving

Reference	Min ID	Max ID	Colours	Coil Length
HEGPV002	2.0	3.0	Grey (GY)	100m
HEGPV003	2.0	5.0	Grey (GY)	100m
HEGPV004	3.0	7.0	Grey (GY)	100m
HEGPV005	4.0	9.0	Grey (GY)	100m
HEGPV006	5.0	11.0	Grey (GY)	100m
HEGPV008	7.0	13.0	Grey (GY)	100m
HEGPV0010	9.0	15.0	Grey (GY)	50m
HEGPV0012	11.0	17.0	Grey (GY)	50m
HEGPV0015	13.0	20.0	Grey (GY)	50m
HEGPV0020	18.0	25.0	Grey (GY)	50m
HEGPV0025	22.0	30.0	Grey (GY)	50m
HEGPV0030	27.0	40.0	Grey (GY)	50m
HEGPV0040	35.0	50.0	Grey (GY)	50m
HEGPV0050	45.0	60.0	Grey (GY)	50m

All dimensions are in mm (nominal) and are subject to technical modification.

Farnell Order Code	Type	Manufacturer Part No.
1168993	HEGPV002	VOG2-3
1168994	HEGPV003	VOG3-6
1168995	HEGPV006	VOG6-10
1168996	HEGPV0010	VOG10-14
1168998	HEGPV0012	VOG12-18
1168999	HEGPV0015	VOG16-22