


Power Entry Modules With Filters

The Schurter power entry modules with filters come in many variations: connector, on/off switch, 1- or 2-pole fuseholder, voltage selector, standard or medical RFI filter. These units are approved at 250 V by a multitude of international agencies including UL, CSA, VDE, SEMKO and SEV.

AC Inlet, 1 and 2-Pole Fuseholder, Switch




Series KMF with RFI filter, fuseholder with EMC shield, 2-pole and On/Off switch. Order fusedrawers separately below. Other filter ratings available.

Stock No.	Mfr.'s Type	Filter (Amps)	Leakage Current	Fuseholder	EACH	
					1-24	25-Up
509-8001	KMF1.1211.11	1 A, Standard	<0.5 mA	1-Pole 5 × 20 mm	17.29	16.89
509-8002	KMF1.1261.11	6 A, Standard	<0.5 mA	1-Pole 5 × 20 mm	17.29	16.89
509-8003	KMF1.1291.11	10 A, Standard	<0.5 mA	1-Pole 5 × 20 mm	17.29	16.89
509-8004	KMF1.1111.11	1 A, Standard	<0.5 mA	2-Pole 5 × 20 mm	19.15	18.75
509-8010	KMF1.1161.11	6 A, Standard	<0.5 mA	2-Pole 5 × 20 mm	19.15	18.75
509-8005	KMF1.1191.11	10 A, Standard	<0.5 mA	2-Pole 5 × 20 mm	19.15	18.75

Fusedrawer (Order Fuses Separately)

509-3304, 4301.1407, 1-pole, 5 × 20 mm with voltage selector, black.....EACH 1.91
509-3308, 4301.1403, 2-pole, 5 × 20 mm without voltage selector, black.....EACH 3.29

AC Inlet with Line Filter, 2-Pole Fuseholder, Switch and Interchangeable Fusedrawers for 1/4" × 1 1/4" or 5 × 20 mm Fuses



Series 4303 and CD with single or double pole shocksafe fuseholder. Inlets available with or without series voltage selection. Series CD with DPST integral switch. Terminals are 4.8 mm × .8 mm quick-connect. Order fusedrawers separately below.


Stock No.	Mfr.'s Type	Filter (Amps)	Leakage Current	D × H × W (mm)	EACH	
					1-24	25-Up
509-4000	4303.5021	1 A, Standard	<0.5 mA	69.5 × 58.0 × 30	19.71	17.74
509-4002	4303.5022	2 A, Standard	<0.5 mA	69.5 × 58.0 × 30	19.71	17.74
509-4004	4303.5023	4 A, Standard	<0.5 mA	69.5 × 58.0 × 30	19.71	17.74
509-4006	4303.5024	6 A, Standard	<0.5 mA	69.5 × 58.0 × 30	19.71	17.74
509-4007	4303.5025	10 A, Standard	<0.5 mA	69.5 × 58.0 × 30	21.17	17.64
509-4008	4303.5225	4 A, Medical	<5.0 µA	69.5 × 58.0 × 30	25.82	23.24
509-4010	4303.5227	6 A, Medical	<5.0 µA	69.5 × 58.0 × 30	25.82	23.24
509-4012	CD14.4101.151	1 A, Standard	<0.5 mA	69.5 × 83.5 × 30	28.56	25.71
509-4014	CD24.4101.151	2 A, Standard	<0.5 mA	69.5 × 83.5 × 30	28.56	25.71
509-4015	CD34.4101.151	4 A, Standard	<0.5 mA	69.5 × 83.5 × 30	28.56	25.71
509-4016	CD64.4101.151	1 A, Medical	<5.0 µA	69.5 × 83.5 × 30	37.40	33.66
509-4018	CDA4.4101.151	2 A, Medical	<5.0 µA	69.5 × 83.5 × 30	37.40	33.66

Fusedrawers

Stock No.	Mfr.'s Type	Voltage Selector	Color	Fuses	EACH	
					1-24	25-Up
509-3011	4303.2401	None	Black	2-Pole, 5 × 20 mm	2.77	1.96
509-3012	4303.2902	None	Grey	2-Pole, 1/4 × 1 1/4"	2.77	1.96
509-4022	4303.2406	None	Black	1-Pole, 5 × 20 mm	1.94	1.67
509-3014	4303.2912	None	Grey	1-Pole, 1/4 × 1 1/4"	6.41	5.32
509-3015	4303.2014.01	100, 120, 220, 240	Black	2-Pole, 5 × 20 mm	5.90	5.16
509-3016	4303.2714.01	100, 120, 220, 240	Grey	2-Pole, 1/4 × 1 1/4"	5.90	5.16
509-4030	4303.2114.01	100, 120, 220, 240	Black	1-Pole, 5 × 20 mm	4.13	3.62
509-4034	4303.2403*	None	Black	2-Pole, 5 × 20 mm	5.30	4.64
509-4036	4303.2904*	None	Grey	2-Pole, 1/4 × 1 1/4"	5.30	4.64
509-4038	4303.2024.01*	100, 120, 220, 240	Black	2-Pole, 5 × 20 mm	6.55	5.73
509-4040	4303.2724.01*	100, 120, 220, 240	Grey	2-Pole, 1/4 × 1 1/4"	6.55	5.73

*Tool accessible only. **Note:** Fusedrawers Must Be Ordered Separately.


AC Inlet with 1-Pole Fuseholders 70°C, 10 A, 250 V



Series 5200 filtered version, series 6200 without filter. Rated up to 10 A/250 V, fuseholder is 1-Pole. Accepts 5 × 20 mm fuse.

Stock No.	Mfr.'s Type	Filter (Amps)	Leakage Current	Mounting	EACH	
					1-24	25-Up
509-1001	5200.0123.1	1 A, Standard	<0.5 mA	Flange	15.45	14.55
509-8602	5200.0143.1	1 A, Standard	<0.5 mA	Snap-in 0.8-3.0 mm	14.17	13.15
509-1002	5200.0623.1	6 A, Standard	<0.5 mA	Flange	15.45	14.55
509-2000	5200.0643.1	6 A, Standard	<0.5 mA	Snap-in 0.8-3.0 mm	19.18	16.73
509-1003	5200.1023.1	10 A, Standard	<0.5 mA	Flange	19.18	16.74
509-1004	5200.1043.1	10 A, Standard	<0.5 mA	Snap-in 0.8-3.0 mm	19.18	16.74
509-1100	6200.2100	Without	—	Flange	2.95	2.39
509-1105	6200.2200	Without	—	Flange	2.95	2.39
509-1110	6200.2300	Without	—	Flange	2.95	2.39
509-1115	6200.4115	Without	—	Snap-in 1.5 mm	2.95	2.39
509-1125	6200.4215	Without	—	Snap-in 1.5 mm	2.95	2.39
509-1125	6200.4315	Without	—	Snap-in 1.5 mm	2.95	2.39

Line Filter with AC Connector, Series Parallel Voltage Selection and Interchangeable FuseDrawers for 1/4" × 1 1/4" or 5 × 20 mm Fuses



Series CE/CG with single or double pole shocksafe fuseholder and series parallel voltage selection. Terminals are 4.8 × 8 mm quick connect. Series CG with DPST integral switch, 70 A in-rush current (3-4 ms).

Stock No.	Mfr.'s Type	Filter (Amps)	Leakage Current	D × H × W (mm)	EACH	
					1-24	25-Up
509-4042	CE10.6100.151	1 A, Standard	<0.5 mA	69 × 69.5 × 30	26.56	23.91
509-4046	CE30.6100.151	4 A, Standard	<0.5 mA	69 × 69.5 × 30	26.56	23.91
509-4048	CE40.6100.151	6 A, Standard	<0.5 mA	69 × 69.5 × 30	26.56	23.91
509-4049	CE60.6100.151	10 A, Standard	<0.5 mA	69 × 69.5 × 30	28.52	25.93
509-4050	CEG0.6100.151	1 A, Medical	<5.0 µA	69 × 69.5 × 30	34.79	31.32
509-4054	CECO.6100.151	4 A, Medical	<5.0 µA	69 × 69.5 × 30	34.79	31.31
509-4056	CEE0.6100.151	6 A, Medical	<5.0 µA	69 × 69.5 × 30	34.79	31.31
509-4058	CG10.6101.151	1 A, Standard	<0.5 mA	69 × 97.0 × 30	37.71	33.94
509-4062	CG30.6101.151	4 A, Standard	<0.5 mA	69 × 97.0 × 30	37.71	33.94
509-4064	CG40.6101.151	6 A, Standard	<0.5 mA	69 × 97.0 × 30	37.71	33.94
509-4066	CG60.6101.151	10 A, Standard	<0.5 mA	69 × 97.0 × 30	40.49	36.81
509-4068	CGG0.6101.151	1 A, Medical	<5.0 µA	69 × 97.0 × 30	49.39	44.36
509-9993	CGCO.6101.151	4 A, Medical	<5.0 µA	69 × 97.0 × 30	49.39	44.36
509-4074	CGL0.6101.151	6 A, Medical	<5.0 µA	69 × 97.0 × 30	49.39	44.36
509-4076	CGL0.6101.151	10 A, Medical	<5.0 µA	69 × 97.0 × 30	52.86	47.47

Voltage Selector

Stock No.	Mfr.'s Type	Markings	EACH	
			1-24	25-Up
509-3027	4305.0048.01	100, 120, 220, 240	4.47	3.43

Note: Voltage Selector Must Be Ordered Separately.

Fusedrawers

Stock No.	Mfr.'s Type	Mounting	Color	EACH	
				1-24	25-Up
509-3023	4305.0001	2-Pole, 5 × 20 mm	Black	3.94	3.49
509-3024	4305.0012	2-Pole, 1/4 × 1 1/4"	Grey	3.94	3.49
509-3025	4305.0021	1-Pole, 5 × 20 mm	Black	5.06	4.48
509-3026	4305.0027	1-Pole, 1/4 × 1 1/4"	Grey	5.06	4.48

Note: Fusedrawers Must Be Ordered Separately.