

531-285.

Type	Side Walls	Pg Knockouts	Inside Height	Ref. No.	Unit
POLYSTYRENE - COVER GREY RAL 7035					
PS 1313- 7	with Pg		63 mm	115-405	14/2
PS 1313-10	with Pg		87 mm	115-905	8/2
PS 1313- 7-o	smooth		63 mm	110-405	14/2
PS 1313-10-o	smooth		87 mm	110-905	8/2
POLYSTYRENE - COVER TRANSPARENT					
PS 1313- 7-t	withPg		63 mm	116-005	14/2
PS 1313-10-t	with Pg		87 mm	116-505	8/2
PS 1313- 7-to	smooth		63 mm	111-005	14/2
PS 1313-10-to	smooth		87 mm	111-505	8/2
POLYCARBONATE - COVER GREY RAL 7035					
PC 1313- 7	with Pg		63 mm	125-405	14/2
PC 1313-10	with Pg		87 mm	125-905	8/2
POLYCARBONATE - COVER TRANSPARENT					
PC 1313- 7-t	with Pg		63 mm	135-005	14/2
PC 1313-10-t	with Pg		87 mm	135-505	8/2

TK 1313

Enclosure

Technical drawing of the TK 1313 enclosure showing top and side views with dimensions.

Knockouts:			= Pg 16/11	= Pg 16	= Pg 21/16	= Pg 29/21
			Max. number of Pg drill holes per box side			
			Pg	A	B	
			7	10	10	
			9	8	8	
			11	8	8	
			13.5	3	3	
			16	3	3	
			21	2	2	
29	2	2				
36	-	-				

All dimensions in millimeters

TK 1313
Empty
Enclosure
130 x 130^{mm}
Type of
Protection
IP 66