

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

,19 .

© COPYRIGHT 19

BY AMP INCORPORATED. ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

G

14

P

LTR

DESCRIPTION

DATE

DWN

APVD

F


REDRAWN PER 0720-0377-94

25OCT94

LO

ME

△ STAMP AMP 16-14*APPROX AS SHOWN



2. WIRE INSUL DIA, 3.05-4.32 [0.120-0.170]

3. TONGUE MATL THK, 0.79±0.05 [0.031±0.002]

1000

LOOSE PIECE

322825

QTY

PACKAGE TYPE

PART NO


AMP INCORPORATED
CUSTOMER SERVICE SYSTEM

MAX RECOMMENDED OPERATING
TEMPERATURE:
343°C [650°F]

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED.
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING
ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:
mm [in]

TOLERANCES UNLESS
OTHERWISE SPECIFIED:



0 PLC ±-
1 PLC ±-
2 PLC ±0.20 [0.008]
3 PLC ±-
4 PLC ±-
ANGLES ±-

MATERIAL
BODY, CU PER ASTM B152
SLEEVE, NI SIL PER
ASTM B122

FINISH
BODY, NP, QQ-N-290

DWN 25OCT94

CHK 25OCT94

M ELLIS

APVD 25OCT94

S BORTNER

PRODUCT SPEC

-

APPLICATION SPEC

-

WEIGHT

-

CUSTOMER DRAWING

AMP AMP Incorporated
Harrisburg, PA 17105-3608

NAME WIRE SPLICE, STRATOTHERM
DIAMOND GRIP, WIRE SIZE,
16-14 AWG

SIZE A3 CAGE CODE 00779 DRAWING NO C-322825

SCALE 6:1 SHEET 1 OF 1 REV F