


Distributed by:

JAMECO[®]
ELECTRONICS

www.Jameco.com ♦ 1-800-831-4242

The content and copyrights of the attached
material are the property of its owner.

Jameco Part Number 170085

MINI GC 25M-F

SPECIFICATION:

1. VOLTAGE RATING: 300VAG(rms).
2. CURRENT RATING: 5 AMP CONTINUOUS
3. DIELECTRIC STRENGTH 1000VAG
4. CONTACT RESISTANCE: 10m Ohm min
5. INSULATION RESISTANCE: 5000 M Ohm min
6. DURABILITY: 30 CYCLES FOR GOLD FLASH
150 CYCLES FOR 15u" GOLD PLATED
7. CORROSION RESISTANCE: MEET MIL-STD-202F METHOD
101 CONDITION BSALT WATER
SPRAY FOR GOLD PLATED OVER 15u"
8. MATING FORCE INSERTION FORCE: 1 OZ-16 OZ
AVERAGE 150 GRAM
EXTRACTION FORCE: 1KG MIN

NOTE: All relevant materials are complied with RoHS directive .

APPROVED		MSL ENTERPRISES CORP.		Cable Length Unless Other Spec. Tolerances: 0 ~0.2M ±0.01M 0.21~1.0M ±0.02M 1.1 ~1.5M ±0.025M 1.51~2.1M ±0.03M 2.1M ↑ ±0.04M
CHECKED	譚小瓊			
DRAWING	易年秀			
ITEM NO.	0028			