






W2E250A Series

Axial

Ø 250mm S-Range

- AC Axial fan with round venturi housing. Shallow depth with external rotor motor for exceptional performance and long life.
- Individual sickle blades made of sheet steel are welded onto the external-rotor motor and dynamically balanced.
- Direction of rotation is CCW looking at rotor.
- Maintenance-free ball bearings..
- Mounting plate with 7 mm holes. Ready to install.
- UL, CSA, VDE approvals on some models, please contact application engineering.

Part Number	Curve	CFM @ 0	VAC	Hertz	Power (W)	dBA	Max Amb. Temp C	Bearing Type	Features	Capacitor (µF)	Grill Position	Wgt. (lbs)
W4S250-CH20-70	3	645	115	50/60	68	61	60	Ball	Leads	-	Dischg	2.69
W4S250-CI20-70	3	645	115	50/60	68	61	60	Ball	Leads	-	Inlet	2.69
W4E250-CH36-70	4	670	115	50/60	48	58	60	Ball	Leads	6	Dischg	3.00
W4E250-CI36-70	4	670	115	50/60	48	58	60	Ball	Leads	6	Inlet	3.00
W2E250-CL08-70	5	1100	115	50/60	160	71	40	Ball	Leads	12	Dischg	3.13
W2E250-CM08-70	5	1100	115	50/60	160	71	40	Ball	Leads	12	Inlet	3.13
W4S250-CH02-70	3	645	230	50/60	68	61	60	Ball	Leads	-	Dischg	2.69
W4S250-CI02-70	3	645	230	50/60	68	61	60	Ball	Leads	-	Inlet	2.69
W4E250-CH02-70	4	670	230	50/60	48	58	60	Ball	Leads	1.5	Dischg	3.00
W4E250-CI02-70	4	670	230	50/60	48	58	60	Ball	Leads	1.5	Inlet	3.00
W2E250-CL06-70	5	1100	230	50/60	160	71	40	Ball	Leads	3	Dischg	3.13
W2E250-CM06-70	5	1100	230	50/60	160	71	40	Ball	Leads	3	Inlet	3.13



ebmpapst

e-mail: sales@us.ebmpapst.com - TEL: 860-674-1515 - FAX: 860-674-8536

ebm-papst Inc., 100 Hyde Road, Farmington, CT 06034 USA

ebm-papst Inc., 2004 © ebm-papst Inc. reserves the right to change any specifications or data without notice