



Features

- RoHS compliant*
- Low profile is compatible with DIPs
- Wide assortment of pin packages enhances design flexibility
- Ammo-pak packaging available
- Recommended for rosin flux and solvent clean or no clean flux processes

- Marking on contrasting background for permanent identification

4600X Series - Thick Film Conformal SIPs

Product Characteristics

Resistance Range 10 ohms to 10 megohms
 Maximum Operating Voltage.....100 V
 Temperature Coefficient of Resistance
 50 Ω to 2.2 megohms ... ±100 ppm/°C
 below 50 Ω..... ±250 ppm/°C
 above 2.2 megohms ±250 ppm/°C
 TCR Tracking..... 50 ppm/°C maximum; equal values
 Resistor Tolerance..... See circuits
 Insulation Resistance
 10,000 megohms minimum
 Dielectric Withstanding Voltage
 200 VRMS
 Operating Temperature
 -55 °C to +125 °C

Environmental Characteristics

TESTS PER MIL-STD-202.....ΔR MAX.
 Short Time Overload ±0.25 %
 Load Life..... ±1.00 %
 Moisture Resistance..... ±0.50 %
 Resistance to Soldering Heat
 ±0.50 %
 Terminal Strength ±0.25 %
 Thermal Shock ±0.25 %

Physical Characteristics

Flammability Conforms to UL94V-0
 Body Material Epoxy resin
 Standard Packaging
 Bulk, Ammo-pak available

How To Order

46 06 X - 101 - 222 LF

Model _____
 (46 = Conformal SIP)
 Number of Pins _____
 Physical Configuration _____
 (X = Thick Film Low Profile)
 Electrical Configuration _____
 • 101 = Bussed
 • 102 = Isolated
 • 104 = Dual Terminator
 • AP1 = Bussed Ammo**
 • AP2 = Isolated Ammo**
 • AP4 = Dual Ammo**
 Resistance Code _____
 • First 2 digits are significant
 • Third digit represents the number of zeros to follow.
 Resistance Tolerance _____
 • Blank = ±2 % (see "Resistance Tolerance" on next page for resistance range)
 • F = ±1 % (100 ohms - 5 megohms)
 Terminations _____
 • All electrical configurations EXCEPT 104 & AP4:
 LF = Sn/Ag/Cu-plated (RoHS compliant)
 • ONLY electrical configurations 104 & AP4:
 L = Sn/Ag/Cu-plated (RoHS compliant)

Consult factory for other available options.

**Available for packages with 10 pins or less.

Package Power Temp. Derating Curve



Package Power Ratings (Watts)

Pkg.	Ambient Temp. 70 °C	Pkg.	Ambient Temp. 70 °C
4604X	0.50	4610X	1.25
4605X	0.63	4611X	1.38
4606X	0.75	4612X	1.50
4607X	0.88	4613X	1.63
4608X	1.00	4614X	1.75
4609X	1.13		

Typical Part Marking


Represents total content. Layout may vary.

Part Number	Marking
4606X-101-RC	6X-1-RC
4608X-102-RC	8X-2-RC
4610X-104-RC/RC	10X-4-RC/RC

RC = ohmic value, 3-digit resistance code.



Product Dimensions



Maximum package length is equal to 2.54mm (.100") times the number of pins, less .005mm (.002").

Governing dimensions are in metric. Dimensions in parentheses are inches and are approximate.

*Terminal centerline to centerline measurements made at point of emergence of the lead from the body.

For Standard Values Used in Capacitors, Inductors, and Resistors, [click here](#).

For information on specific applications,
download Bourns' application notes:

- [DRAM Applications](#)
- [Dual Terminator Resistor Networks](#)
- [R/2R Ladder Networks](#)
- [SCSI Applications](#)

4600X Series - Thick Film Conformal SIPs

BOURNS®

Isolated Resistors (102 Circuit)

Model 4600X-102-RC
4, 6, 8, 10, 12, 14 Pin



These models incorporate 2 to 7
isolated thick-film resistors of equal
value, each connected between two
pins.

Resistance Tolerance

10 ohms to 49 ohms±1 ohm
50 ohms to 5 megohms±2 %*
Above 5 megohms ±5 %

Power Rating per Resistor

At 70 °C 0.30 watt

Power Temperature Derating Curve



Bussed Resistors (101 Circuit)

Model 4600X-101-RC
4 through 14 Pin



These models incorporate 3 to 13
thick-film resistors of equal value, each
connected between a common bus
(pin 1) and a separate pin.

Resistance Tolerance

10 ohms to 49 ohms±1 ohm
50 ohms to 5 megohms±2 %*
Above 5 megohms ±5 %

Power Rating per Resistor

At 70 °C 0.20 watt

Power Temperature Derating Curve



Dual Terminator (104 Circuit)

Model 4600X-104-R1/R2
4 through 14 Pin



The 4608X-104 (shown above) is an 8-
pin configuration and terminates 6 lines.
Pins 1 and 8 are common for ground
and power, respectively. Twelve thick-
film resistors are paired in series be-
tween the common lines (pins 1 and 8).

Resistance Tolerance

Below 100 ohms.....±2 ohms
100 ohms to 5 megohms±2 %*
Above 5 megohms ±5 %

Power Rating per Resistor

At 70 °C 0.20 watt

Power Temperature Derating Curve



Popular Resistance Values (101, 102 Circuits)**

Ohms	Code	Ohms	Code	Ohms	Code	Ohms	Code	Ohms	Code
10	100	180	181	1,800	182	15,000	153	120,000	124
22	220	270	271	2,200	222	18,000	183	150,000	154
27	270	330	331	2,700	272	20,000	203	180,000	184
33	330	390	391	3,300	332	22,000	223	220,000	224
39	390	470	471	3,900	392	27,000	273	270,000	274
47	470	560	561	4,700	472	33,000	333	330,000	334
56	560	680	681	5,600	562	39,000	393	390,000	394
68	680	820	821	6,800	682	47,000	473	470,000	474
82	820	1,000	102	8,200	822	56,000	563	560,000	564
100	101	1,200	122	10,000	103	68,000	683	680,000	684
120	121	1,500	152	12,000	123	82,000	823	820,000	824
150	151					100,000	104	1,000,000	105

* ±1 % tolerance is available by adding suffix code "F" after the resistance code.

**Non-standard values available, within resistance range.

Popular Resistance Values (104 Circuit)**

Resistance			
Ohms		Code	
R ₁	R ₂	R ₁	R ₂
160	240	161	241
180	390	181	391
220	270	221	271
220	330	221	331
330	390	331	391
330	470	331	471
3,000	6,200	302	622

REV. 04/10

Specifications are subject to change without notice.
Customers should verify actual device performance in their specific applications.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Bourns:

[4608X-101-153](#) [4606X-101-561](#) [4605X-101-124](#) [4608X-102-304F](#) [4606X-101-514](#) [4608X-102-304](#) [4610X-101-111F](#) [4610X-101-271](#) [4608X-102-303F](#) [4610X-102-563F](#) [4610X-102-564](#) [4606X-102-101F](#) [4605X-101-272](#) [4610X-R2R-471](#) [4605X-101-225](#) [4606X-102-821](#) [4606X-102-104](#) [4608X-1T1-102](#) [4610X-102-151](#) [4607X-101-104](#) [4614X-101-681](#) [4610X-102-111](#) [4608X-101-103F](#) [4606X-AP1-333](#) [4614X-102-823](#) [4604X-102-561F](#) [4610X-102-121](#) [4606X-102-103F](#) [4606X-1T1-101](#) [4610X-101-513](#) [4608X-1T1-202](#) [4610X-102-101](#) [4610X-102-181](#) [4610X-101-563](#) [4610X-102-161](#) [4608X-101-104F](#) [4610X-101-123](#) [4610X-101-183](#) [4606X-102-104F](#) [4610X-101-153](#) [4609X-1T1-102](#) [4608X-104-302/622](#) [4609X-1T1-105](#) [4610X-AP1-473](#) [4606X-102-471](#) [4609X-101-821](#) [4610X-AP1-681](#) [4606X-101-823](#) [4614X-102-473](#) [4610X-101-103](#) [4604X-101-822](#) [4605X-101-751](#) [4606X-AP1-561](#) [4610X-AP1-201](#) [4610X-AP1-202](#) [4610X-101-251F](#) [4606X-1T1-102](#) [4610X-AP1-273](#) [4606X-101-473](#) [4604X-102-562](#) [4610X-102-565](#) [4610X-AP1-562](#) [4610X-101-224F](#) [4606X-102-184](#) [4610X-102-562](#) [4610X-102-512](#) [4610X-AP1-512](#) [4612X-102-272](#) [4609X-101-471](#) [4612X-102-242](#) [4612X-102-222](#) [4604X-102-515](#) [4607X-101-123](#) [4606X-102-204](#) [4608X-101-322](#) [4612X-101-151](#) [4607X-101-153](#) [4608X-1T2-220](#) [4608X-1T2-151](#) [4612X-101-563](#) [4608X-1T2-330](#) [4605X-101-684](#) [4608X-1T2-121](#) [4610X-102-824](#) [4610X-102-823F](#) [4608X-1T2-470](#) [4610X-104-181/391](#) [4608X-102-144](#) [4608X-1T2-150](#) [4612X-101-103](#) [4608X-1T2-101](#) [4608X-1T2-560](#) [4608X-104-221/331](#) [4604X-102-363](#) [4605X-101-112](#) [4609X-101-184](#) [4612X-102-681](#) [4610X-AP2-391](#) [4610X-102-560](#) [4610X-102-390](#)