





PRODUCT NO.
SEE TABLE




COVER
MATERIAL: 30% GLASS-FILLED POLYESTER,
FLAME RETARTANT PER UL 94 V-0,
COLOR: BLUE




MATERIAL: PHOSPHORUS BRONZE,
FULL HARD. SEE TABLE AND
NOTES FOR PLATING.




SECTION X-X



P. C. B. HOLE PATTERN
CONNECTOR SIDE OF P. C. BOARD SHOWN (NOTE 3)
SCALE 4/1



mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY		 www.fciconnect.com		
litr	ecn no	dr	date	linear	.XX ±.01		projection 	title QUICKIE P.C.B. CONNECTOR 16,20,24,40,60,& 64		
M	V11057	JM	6/11/91		.XXX ±.005					
N	V82154	CGC	12/15/98		.XXXX ±.0020					
P	N05-0329	DT	12/09/05	angles	0° ±2°		 scale 2.5:1	product family		code
R	N07-0199	WG	08/27/07	dr	J.MUSTARD	6/11/91		size dwg no		NAN
				engr	M.SMYK	6/11/91				
				chr	W.FUNK	6/11/91				
				appd	M.SMYK	6/11/91			sheet 1 of 2	
sheet index	revision	R	R							
	sheet	1	2							



A



B

PRODUCT NO.	NO. OF POS.	DIM "A"	DIM "B"	DIM "C" REF	SEE NOTE
65494-009/009LF	20	. 950/24. 13	1. 200/30. 48	. 100/2. 54	1
-010/010LF					2
-011/011LF				. 156/3. 96	1
-012/012LF					2
-013/013LF	40	1. 950/49. 53	2. 200/55. 88	. 100/2. 54	1
-014/014LF					2
-015/015LF				. 156/3. 96	1
-016/016LF					2
-017/017LF	16	. 750/19. 05	1. 000/2. 54	. 100/2. 54	1
-018/018LF					2
-019/019LF				. 156/3. 96	1
-020/020LF					2
-021/021LF	60	2. 950/74. 93	3. 200/81. 28	. 100/2. 54	1
-022/022LF					2
-023/023LF				. 156/3. 96	1
-024/024LF					2
-025/025LF	64	3. 150/80. 01	3. 400/86. 36	. 100/2. 54	1
-026/026LF					2
-027/027LF				. 156/3. 96	1
-028/028LF					2
-029/029LF	24	1. 150/29. 21	1. 400/35. 56	. 100/2. 54	1
-030/030LF					2
-031/031LF				. 156/3. 96	1
-032/032LF					2
-033/033LF	44	2. 150/54. 61	2. 400/60. 96	. 100/2. 54	1
-034/034LF					2
-035/035LF				. 156/3. 96	1
65494-036/036LF					2

NOTES:

- ① 50u"/1.27uM MIN. Ni UNDERPLATE OVER ENTIRE TERMINAL AND Au FLASH ON SOLDER TAIL ONLY.
2. THE P/N WITH "LF" SUFFIX IS LEAD FREE PART NUMBER;
- ③ 65494-***: 150u"/3.81uM MIN. TIN/LEAD 93/7 OVER ENTIRE TERMINAL.
65494-***LF 150u"/3.81uM MIN. MATTE TIN OVER ENTIRE TERMINAL.
- ④ SEE TA 246 FOR MORE INFORMATION.
5. THE PACKAGING FOR THE LEAD FREE P/N MEETS GS-14-920 SPECIFICATION;
6. FOR LEAD FREE P/N THE PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATION AS DESCRIBED IN GS-22-008;
7. FOR LEAD FREE P/N, THE HOUSING WILL WITHSTAND EXPOSURE TO 260 DEGREE C FOR 10 SECONDS IN A WAVE SOLDER APPLICATION.

A

mat'l. code				tolerances unless otherwise specified				CUSTOMER COPY		 www.fciconnect.com		
ltr	ecn no	dr	date	linear	.XX ±.01/.0±.3			projection	title			
R					.XXX ±.005/.00±.13				QUICKIE P.C.B CONNECTOR			
				angles	.XXX ±.0020/.000±.051				16,20,24,40,60,& 64			
					0° ±2°				product family			
				dr	J.MUSTARD	6/11/91	INCH/MM		code			
				enrg	M.SMYK	6/11/91	scale	size dwg no				
				chr	W.FUNK	6/11/91		NAN				
				appd	M.SMYK	6/11/91	1:1	sheet				
sheet	revision						A			65494		
index	sheet									2 of		

B