



! Discontinued

## Overview

Lead time	Usually in Stock
-----------	------------------

## General

Provided equipment	CD with software Rack mounting brackets Rack mounting support rails Smart UPS signalling RS-232 cable User manual USB cable
--------------------	--

## Physical

Number of rack unit	2U
Colour	Black
Depth	45.7 cm
Height	8.9 cm
Net weight	21.82 kg
Width	43.2 cm

## Input

Network frequency	50/60 Hz +/- 3 Hz auto-sensing
Plug standard	IEC 320 C14
Input voltage limits	151...302 V adjustable 160...286 V
Input voltage	230 V

## Output

Rated power in W	480 W
Maximum configurable power in W	480 W
Harmonic distortion	Less than 5 % at full load

Output frequency	47...53 Hz for 50 Hz nominal sync to mains 57...63 Hz for 60 Hz nominal sync to mains
Crest factor	Up to 5 : 1
UPS type	Line interactive
Wave type	Sine wave
Nb of power socket outlets	4 IEC 320 C13 2 IEC Jumpers
Output voltage	230 V

## Conformance

Product certifications	C-Tick CE TÜV VDE
Standards	EN 50091-1 EN 50091-2

## Environmental

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-15...45 °C
Storage altitude	0.00...15240.00 m
Acoustic level	36 dBA
Heat dissipation	68 Btu/h

## Batteries & Runtime

Battery type	Lead-acid battery
Number of battery filled slots	0
Number of battery free slots	0
Battery recharge time	3 h
Number of battery replacement quantity	1
Additional information	Configurable for 220 : 230 or 240 nominal output voltage
Liquid value	0

## Communications & Management

Free slots	1
Control panel	LED status display with load and battery bar-graphs and on line : on battery : replace battery : and overload indicators
Alarm	Alarm when on battery : distinctive low battery alarm : configurable delays
Emergency power off	Optional

## Surge Protection and Filtering

Surge energy rate	480 J
Noise suppression	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : meets UL 1449

## Packing Units

Package 1 Weight	25.11 kg
Package 1 Height	25.4 cm
Package 1 width	59.4 cm
Package 1 Length	60.3 cm

Number of Units in Package 2	1
Number of Units in Package 3	8

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

### Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

### SUA750RMI2U is replaced by:



#### Smart-UPS SMT750RMI2U

APC Smart-ups 750VA LCD RM 2U 230V

Qty 1

Reason for Substitution: End of life | Substitution date: 15 June 2020 | Migration SPD