

Power Quality Products

Isolated Ground Devices

Straight Blade Receptacles



Isolated Ground, Straight Blade, Duplex and Single Receptacles

Rating	NEMA Number	NEMA Configuration	Description	Catalog Numbers
15A 125V	5-15R		Duplex, orange.	IG5262
			Duplex, ivory.	IG5262I
			Duplex, red.	IG5262R
			Duplex, gray.	IG5262GY
			Duplex, orange.	CR5252IG
			Duplex, black.	CR5252IGBK
			Duplex, gray.	CR5252IGGY
			Duplex, ivory.	CR5252IGI
			Duplex, office white.	CR5252IGOW
			Duplex, white.	CR5252IGW
			Style Line® orange, duplex.	IG2152
			4-PLEX® orange.	IG415
20A 125V	5-20R		Single, orange.	IG5261
			Duplex, orange.	IG5362
			Duplex, ivory.	IG5362I
			Duplex, gray.	IG5362GY
			Duplex, white.	IG5362W
			Duplex, red.	IG5362R
			Duplex, orange.	CR5352IG
			Duplex, black.	CR5352IGBK
			Duplex, gray.	CR5352IGGY
			Duplex, ivory.	CR5352IGI
			Duplex, office white.	CR5352IGOW
			Duplex, white.	CR5352IGW
15A 250V	6-15R		Style Line® orange, duplex.	IG2162
			Style Line® gray, duplex.	IG2162GY
			4-PLEX® orange.	IG420
20A 250V	6-20R		Single, orange.	IG5361
			Duplex, orange.	IG5662
			Single, orange.	IG5661
30A 125V	5-30R		Duplex, orange.	IG5462
			Single, orange.	IG5461
30A 250V	6-30R		Single, orange.	IG9308
			Single, orange.	IG9330

Hospital Grade, Isolated Ground, Straight Blade Receptacles

Rating	NEMA Number	NEMA Configuration	Description	Catalog Numbers
15A 125V	5-15R		Duplex, orange.	IG8200
			Duplex, red.	IG8200R
			Single, orange.	IG8210
20A 125V	5-20R		Duplex, orange.	IG8300
			Duplex, red.	IG8300R
			Style Line® orange.	IG2182
			Style Line® ivory.	IG2182I
			Style Line® white.	IG2182WA
			Single, orange.	IG8310

Note: Accessories for 4-PLEX Receptacles located on page A-9.

