




CATALOG NUMBER:	See table below
CUSTOMER:	Stock
DESCRIPTION:	Outdoor use extension cord incorporating type SJTW cable
APPROVALS:	UL Listed and CSA Certified Outdoor Use Cord Set

CONSTRUCTION PARAMETERS:

Conductor:	See table below
Jacket material:	PVC
Overall cable O.D. (nom):	See table below
Cord rating:	Hard Usage per the National Electric Code
Cable legend:	Indent print
Attachment plug configuration:	NEMA 5-15P
Cord connector configuration:	NEMA 5-15R
Plug and connector material:	PVC



ELECTRICAL PROPERTIES:

Cable temperature rating:	-20 to +60 °C
Nominal operating voltage:	125 VAC
Maximum operating current:	See table below

Catalog number	Length	Conductor	Cable O.D. (nom)	Current rating	
02304	10 ft	16/3 26/30 BC	0.315 in	13A	
02305	15 ft				
02306	15 ft				
02307	25 ft				
02308	50 ft				
02309	100 ft			10 A	
02407	25 ft	14/3 41/30 BC	0.352 in	15A	
02408	50 ft			13A	
02409	100 ft				
02507	25 ft	12/3 65/30 BC	0.420 in	15A	
02508	50 ft				
02509	100 ft				
02607	25 ft	10/3 104/30 BC	0.567 in		
02608	50 ft				
02609	100 ft				

The information presented here is, to the best of our knowledge, true and accurate. However, since conditions of use are beyond our control, all recommendations or suggestions are presented without guarantee or responsibility on our part. We disclaim all liability in connection with the use of information contained herein or otherwise.

This specification is proprietary intellectual property of Coleman Cable Systems. Any information contained herein shall not be disclosed to any party without written consent of Coleman Cable Systems.