


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	K8	REVISED PER ECR-17-000959	25FEB2017	RS	DR

AMP

WIRE RANGE

6 AWG
SOLID OR STRANDED



- 1
- STAMP AMP 6W* APPROX AS SHOWN.

2

3

4

5

6

7

8

9

10

PRELIMINARY	170°C[338°F]	4 5	20	6	LOOSE PIECE, BOX	8-34319-5
	343°C[650°F]	----	500	10	LOOSE PIECE	34319-4
	260°C[500°F]	----	500	8	LOOSE PIECE	34319-3
	170°C[338°F]	----	100	7	LOOSE PIECE	34319-1
	170°C[338°F]	4 5	500	6	LOOSE PIECE	34319
MAX. OPERATING TEMP.		APPROVALS	QTY	FINISH	PACKAGE TYPE	PART NO.

AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

MAX RECOMMENDED OPERATING TEMPERATURE:
SEE TABLE

FOR ADDITIONAL
PRODUCT INFORMATION OR
COPIES OF DRAWINGS
AND TECHNICAL DOCUMENTS

PRODUCT INFORMATION CENTER
1-800-522-6752

FOR APPLICATION
TOOLING INFORMATION

TOOLING ASSISTANCE CENTER
1-800-722-1111

FOR ORDER ENTRY

1-800-526-5142

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

VOLTAGE RATING:
N/A

CIRCULAR MIL AREA:
10.5-16.8mm²[20,800-33,100]
SOLID OR STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
TA BRINKMAN
CHK
DA PATTERSON
APVD
DA PATTERSON

DIMENSIONS:
mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± -
4 PLC ± -
ANGLES ± -

MATERIAL

FINISH

SEE TABLE

SEE TABLE

4-14-93
4-14-93
4-14-93

NAME

PRODUCT SPEC

APPLICATION SPEC

SIZE
CAGE CODE
DRAWING NO

RESTRICTED TO

SCALE
SHEET

10:1
1 OF 1

REV
K8

TE Connectivity

SPLICE, PARALLEL,
SOLISTRAND

A200779C=34319

CUSTOMER DRAWING