

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

AUG ,2006.

COPYRIGHT

BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.

LOC
DWDIST
—

REVISIONS

P LTR

DESCRIPTION

DATE

DWN

APVD







C

REVISED (ECR-13-003844)

04JUN13

JL

WK



NOTE:

- MATERIAL:
HOUSING: THERMOPLASTIC(LCP),
UL 94V-0, COLOR: NATURE.
ACTUATOR: THERMOPLASTIC, UL 94 V-0,
COLOR: IVORY.
HOLD DOWN: PHOSPHOR BRONZE.
CONTACT: PHOSPHOR BRONZE.
- FINISH:
CONTACT: GOLD FLASH OVER ALL,
50u" MIN. NICKEL UNDERPLATED ALL OVER.
HOLD DOWN: 100u" MIN. BRIGHT TIN PLATING OVER,
50u" MIN. NICKEL UNDERPLATED ALL OVER.
WITHOUT AMP LOGO FOR 12 POSITION UNDER

24.50	25.60	30.43	50	5-1734592-0
24.00	25.10	29.93	49	4-1734592-9
23.50	24.60	29.43	48	4-1734592-8
23.00	24.10	28.93	47	4-1734592-7
22.50	23.60	28.43	46	4-1734592-6
22.00	23.10	27.63	45	4-1734592-5
21.50	22.60	27.43	44	4-1734592-4
21.00	22.10	26.93	43	4-1734592-3
20.50	21.60	26.43	42	4-1734592-2
20.00	21.10	25.93	41	4-1734592-1
19.50	20.60	25.43	40	4-1734592-0
19.00	20.10	24.93	39	3-1734592-9
18.50	19.60	24.43	38	3-1734592-8
18.00	19.10	23.93	37	3-1734592-7
17.50	18.60	23.43	36	3-1734592-6
17.00	18.10	22.93	35	3-1734592-5
16.50	17.60	22.43	34	3-1734592-4
16.00	17.10	21.93	33	3-1734592-3
15.50	16.60	21.43	32	3-1734592-2
15.00	16.10	20.93	31	3-1734592-1
14.50	15.60	20.43	30	3-1734592-0
14.00	15.10	19.93	29	2-1734592-9
13.50	14.60	19.43	28	2-1734592-8
13.00	14.10	18.93	27	2-1734592-7
12.50	13.60	18.43	26	2-1734592-6
12.00	13.10	17.93	25	2-1734592-5
11.50	12.60	17.43	24	2-1734592-4
11.00	12.10	16.93	23	2-1734592-3
10.50	11.60	16.43	22	2-1734592-2
10.00	11.10	15.93	21	2-1734592-1
9.50	10.60	15.43	20	2-1734592-0
9.00	10.10	14.93	19	1-1734592-9
8.50	9.60	14.43	18	1-1734592-8
8.00	9.10	13.93	17	1-1734592-7
7.50	8.60	13.43	16	1-1734592-6
7.00	8.10	12.93	15	1-1734592-5
6.50	7.60	12.43	14	1-1734592-4
6.00	7.10	11.93	13	1-1734592-3
5.50	6.60	11.43	12	1-1734592-2
5.00	6.10	10.93	11	1-1734592-1
4.50	5.60	10.43	10	1-1734592-0
4.00	5.10	9.93	09	0-1734592-9
3.50	4.60	9.43	08	0-1734592-8
3.00	4.10	8.93	07	0-1734592-7
2.50	3.60	8.43	06	0-1734592-6
2.00	3.10	7.93	05	0-1734592-5
C	B	A	POS.	PART NUMBER
DIMENSIONS				

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN J. LAI 15APR2009

CHK S. CHIEN 15APR2009

APVD W. KODAMA 15APR2009

PRODUCT SPEC

108-57523

QUALIFICATION TEST REPORT


501-57598

WEIGHT - GRAMS

CUSTOMER DRAWING

DIMENSIONS:

MM



TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	± -
1 PLC	± 0.35
2 PLC	± 0.25
3 PLC	± -
4 PLC	± -
ANGLES	± 3°

MATERIAL

SEE NOTE

FINISH

SEE NOTE

STE

TE Connectivity

NAME

FPC CONNECTOR, 0.5mm PITCH, BOTTOM CONTACT, SMT TYPE.

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO


A3 00779 C=1734592

SCALE

SHEET

1 OF 3

REV C



TOLERANCE ± 0.05

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC.

L

1

CUSTOMER DRAWING

DIMENSIONS:

MM

MATERIAL

TOI FRANCES UNLESS

OTHERWISE SPECIFIED:

0. PLC + -

1	PLC	± 0.35
2	PLC	± 0.25
3	PLC	$\pm -$

4. FLEC	±	
ANGLES		± 3°

Circumstance	Percentage of Respondents (%)
Self-defense	85
To protect others	75
To protect property	80
To protect the community	65
To protect the environment	70



TE Connectivity

NAME

FPC CONNECTOR, 0.5mm PITCH, BOTTOM CONTACT,
SMT TYPE.

SIZE

CAGE CODE

DRAWING NO

9 | © = 1734592

RESTRICTED TO

SCALE

SHEET

REV	
-----	--

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

AUG ,2006.

© COPYRIGHT

BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR



DESCRIPTION

DATE

DWN


APVD

SEE SHEET 1.



NOTE :

1. TAPE REEL:
DIAMETER: 13", THICKNESS : 0.35±0.05mm.
2. CARTON:
SIZE: 350mm(L)X 350mm(W)X 340mm(H).



12000	2000	44.00	26.70	30.55	31.50	50	
		44.00	26.20	30.05	31.00	49	
		44.00	25.70	29.55	30.50	48	
		44.00	25.20	29.05	30.00	47	
		44.00	24.70	28.55	29.50	46	
		44.00	24.20	28.05	29.00	45	
		44.00	23.70	27.55	28.50	44	
		44.00	23.20	27.05	28.00	43	
		44.00	22.70	26.55	27.50	42	
		44.00	22.20	26.05	27.00	41	
		44.00	21.70	25.55	26.50	40	
		44.00	21.20	25.05	26.00	39	
		44.00	20.70	24.55	25.50	38	
		44.00	20.20	24.05	25.00	37	
		44.00	19.70	23.55	24.50	36	
		44.00	19.20	23.05	24.00	35	
16000		44.00	18.70	22.55	23.50	34	
		44.00	18.20	22.05	23.00	33	
		44.00	17.70	21.55	22.50	32	
		44.00	17.20	21.05	22.00	31	
		32.00	16.70	20.55	21.50	30	
		32.00	16.20	20.05	21.00	29	
		32.00	15.70	19.55	20.50	28	
		32.00	15.20	19.05	20.00	27	
		32.00	14.70	18.55	19.50	26	
		32.00	14.20	18.05	19.00	25	
		32.00	13.70	17.55	18.50	24	
		32.00	13.20	17.05	18.00	23	
		32.00	12.70	16.55	17.50	22	
		32.00	12.20	16.05	17.00	21	
		20000	24.00	11.70	15.55	16.50	20
			24.00	11.20	15.05	16.00	19
24.00			10.70	14.55	15.50	18	
24.00			10.20	14.05	15.00	17	
24.00			9.70	13.55	14.50	16	
24.00			9.20	13.05	14.00	15	
24.00			8.70	12.55	13.50	14	
24.00			8.20	12.05	13.00	13	
24.00			7.70	11.55	12.50	12	
24.00			7.20	11.05	12.00	11	
24.00			6.70	10.55	11.50	10	
24.00			6.20	10.05	11.00	09	
24.00			5.70	9.55	10.50	08	
24.00			5.20	9.05	10.00	07	
24.00			4.70	8.55	9.50	06	
24.00			4.20	8.05	9.00	05	
APQ (PCS/CARTON)	PPQ (PCS/REEL)	D	C	B	A	POS.	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	 TE Connectivity			
DIMENSIONS: MM		CHK				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD				
0 PLC ± -		PRODUCT SPEC				
1 PLC ± -		APPLICATION SPEC	NAME FPC CONNECTOR, 0.5mm PITCH, BOTTOM CONTACT, SMT TYPE.			
2 PLC ± -		WEIGHT	SIZE A3			
3 PLC ± -		CUSTOMER DRAWING	CAGE CODE 00779			
4 PLC ± -			DRAWING NO C=1734592			
ANGLES ± -			RESTRICTED TO			
FINISH			SCALE			
			SHEET 3 OF 3			
			REV C			