

USBC SERIES

USB 2.0 CABLE PLUGS

SPECIFICATIONS

For complete specifications see www.samtec.com?USBC

Insulator Material:

Glass Filled Thermoplastic

Contact Material:

Copper Alloy

Shell Material:

Cold Rolled Steel

(0,30 mm) .012" thickness

Plating:

Gold on Contacts,

Nickel on Shell, Tin on Tails

Operating Temp Range:

0°C to +50°C

Current Rating:

1.0A per contact

Voltage Rating:

30 VAC (R.M.S.)

Contact Resistance:

30 mΩ

Minimum Cycles:

5000

RoHS Compliant:

Yes

TID Numbers:

USBC-AM-BM-B-B-S-3

(60000217)

USBC-MA-MB-B-B-S-3

(60000228)

USBC-AM-MB-B-B-S-3


(60000223)

Mates with:

MUSB, USB,

USBR, SPM

USBC-AM-BM-B-B-S-2




USBC-MA-MB-B-B-S-2

Variety of wire lengths

Double Ended

Micro & Mini USB, USB-A and USB-B Type end options



Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM