


1) Nur für Buchanan Crimpwerkzeug Einstellø 1,0
only for Buchanan crimping tool adjusting ø0,1



Bestell-Nummer versilbert <i>silver plated</i>	/ Part No. vergoldet <i>gold plated</i>	D	Leiterquerschnitt <i>wire gauge</i>		Abisolierlänge der Litze <i>stripping length</i>	-
			mm²	AWG		
09 15 000 6204	09 15 000 6224	0,90	0,14-0,37	26-22	8	1)
09 15 000 6203	09 15 000 6223	1,10	0,5	20		
09 15 000 6205	09 15 000 6225	1,30	0,75	18		
09 15 000 6202	09 15 000 6222	1,45	1	18		
09 15 000 6201	09 15 000 6221	1,75	1,5	16		
09 15 000 6206	09 15 000 6226	2,25	2,5	14	6	
09 15 000 6207	09 15 000 6227	0,90	0,14-0,37	26-22	8	

			All Dimensions in mm Original Size DIN A 4				Techn. Character.			Nicht tolerierte Maße/ Free size tolerances			
					Dat.	Name	Maßstab/ Scale 2:1	Han D / Buchsenkontakt Crimpkontakt gedreht 10A <i>crimpcontact twisted 10A</i>					
				Detail.	16.06.10	Rull							
				Insp.		Sch							
				Stand.									
					HARTING Electric GmbH & Co. KG					TB 09 15 000 62..			Blatt/ page /
A				D-32339 Espelkamp									
Mod.	Dat.	Name								Sub. TB 09 15 000 62.. v. 22.03.99			