





SMA Connectors (Continued)
Panel Mount, Straight Terminal

4 Hole Flange Mount Jack Receptacle




Body Material & Finish	Contact Captivation	RF Leakage db min.	Temperature Range	M/A-COM Model No.	Part No.
Stainless, Passivated	None	-(100-fGHz)	-65 to 165° C	2052-1200-02	1052518-1
Stainless, Passivated	Epoxy	-(60-fGHz)	-65 to 125° C	2052-1201-02	1052523-1
Stainless, Gold	Epoxy	-(60-fGHz)	-65 to 125° C	2052-1201-00	1052522-1

2 Hole Flange Mount Plug Receptacle



Body Material & Finish	Contact Captivation	RF Leakage db min.	Temperature Range	M/A-COM Model No.	Part No.
Stainless, Passivated	Epoxy	-(60-fGHz)	-65 to 125° C	2051-1352-02	1052349-1

2 Hole Flange Mount Jack Receptacle



Body Material & Finish	Contact Captivation	RF Leakage db min.	Temperature Range	M/A-COM Model No.	Part No.
Stainless, Passivated	None	-(100-fGHz)	-65 to 165° C	2052-1351-02	1052548-1
Stainless, Passivated	Epoxy	-(60-fGHz)	-65 to 125° C	2052-1352-02	1052552-1