







- | | | | |
|--------------------|---|----------------|----------------|
| NATURAL | 0.00008 MIN | 4.20 | 1888669-9 |
| | | 3.38 | 1888669-8 |
| NATURAL | 0.00038 MIN | 2.87 | 1888669-7 |
| | | 4.20 | 1888669-6 |
| | | 3.38 | 1888669-5 |
| NATURAL | 0.00076 MIN | 2.87 | 1888669-4 |
| | | 4.20 | 1888669-3 |
| | | 3.38 | 1888669-2 |
| EXTRACTOR
COLOR | CONTACT GOLD
INTERFACE  | TAIL
LENGTH | PART
NUMBER |


4805 (3/11)

LOC		DIST		REVISIONS				
GP	00	F	LYR	DESCRIPTION	DATE	DWN	APVD	
		-	-	SEE SHEET 1	-	-	-	



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D. RINGLER 29SEP2006	 TE Connectivity	
DIMENSIONS:		CHK J. PENNYPACKER 29SEP2006		
mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD M. BOWERS 22DEC2006	NAME	
	9 PLG ±.5	PRODUCT SPEC	SOCKET ASSEMBLY, DDR2 VLP DIMM, SOLDER TAIL, 240 POSITION	
	1 PLG ±0.13	108-2111		
	5 PLG ±0.013	APPLICATION SPEC		
MATERIAL	4 PLG ±0.0001	114-13087	SIZE	CAGE CODE
	FINISH	WEIGHT	A100779	C=1888669
CUSTOMER DRAWING		RESTRICTED TO		
		SCALE	4:1	SHEET 2 OF 3
		REV A2		



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D. RINGLER 29SEP2006 CHK J. PENNYACKER 29SEP2006 M. BOWERS 22DEC2006		 TE Connectivity	
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
mm		0 PLC ±.1 1 PLC ±0.5 2 PLC ±0.13 3 PLC ±0.013 4 PLC ±0.001 ANGLES .°		SOCKET ASSEMBLY, DDR2 VLP DIMM, SOLDER TAIL, 240 POSITION	
		PRODUCT SPEC 108-2111 APPLICATION SPEC 114-13087		SIZE A1	
MATERIAL		FINISH		CAGE CODE	
-		-		DRAWING NO	
-		-		100779	
-		-		C1888669	
-		-		SCALE	
-		-		1:1	
-		-		SHEET 3 of 3	
-		-		REV A2	
-		-		CUSTOMER DRAWING	
-		-		RESTRICTED TO	
-		-		-	