

Search Results

Evaluate
- FAQ's
How to Buy
- Bill of Material
- Favorite Products List
- Locate Distributor

Home > Product On-Line Catalog > Search Results >

Current refinements (click to remove) Search Tips

Text Search: 'F512D6-6M9Y'

Your search criteria matched only one product, shown below

F512D6-6M9Y



- Pass all TIA/EIA-568-B.3 performance requirements
- FOCIS-5 compliant
- Insertion loss per mated pair: 0.50dB typical; 0.75dB max.
- Factory terminated and 100% tested for insertion loss
- Insertion loss data recorded for every multimode cable assembly
- Lifetime traceability of test data to a Q.C. number on each cable assembly

* MTP is a registered trademark of US Conec Ltd.

• Part Number	F512D6-6M9Y
• RoHS Compliance Status	Compliant
• Note	Intended for use in fixed installations which are outside the scope of RoHS
• Part Description	Male MTP* to male MTP* plenum rated 12-fiber interconnect cable assembly (one male MTP* connector on each end on ribbon interconnect cable) – 50/125µm. Outside diameter: 5mm x 2.5mm.
• Product Type	MTP* Interconnect Cable Assemblies
• Length (m)	9
• Fiber Compatibility	50/125µm
• Fiber Cable Size	5mm x 2.5mm
• Fiber Type	Multimode
• Connector 1 Type	Male MTP*
• Connector 2 Type	Male MTP*
• Fiber Count	12
• Flammability Rating	Plenum (OFNP)
• Pricing Description	Male MTP*- Male MTP* Ribbon Interconnect Cable Assembly OM2 50µm, OFNP, 9m
• Min. Order UOM	PC
• Min. Order Qty.	1
• BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
• Add to Favorite Product List	<input type="checkbox"/>

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.