





Dimensions: mm (In.)

**Electrical Specifications:**

- Rating: 5A / 120VAC or 28VDC; 2A / 250VAC
- Contact resistance: 10mΩ max. initially
- Electrical life: 30,000 actuations
- Insulation resistance: 1000MΩ min.
- Dielectric strength: 1,000VRMS @ sea level

Mechanical Specifications:

- Circuit: SPDT, On-On
- Operating temperature: -30°C ~ +85°C

Materials:

- Case: diallyl phthalate (DAP)
- Housing: stainless steel
- Slide handle: nylon
- End terminals: silver plated coin silver
- Center contacts & body: silver plated brass

Sub-Miniature Slide Switch
102-1271

**Mountain
Switch**

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[102-1271](#)