








PANEL MOUNTING



- NOTE:
1. ALL DIMENSIONS IN MM [INCH]
 2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
 3. TERMINAL NUMBERS FOR REF ONLY
 4. RATING: 5A @ 250 VAC
6A @ 24 VDC
8A @ 125 VAC
 5. ELECTRIC LIFE: 50,000 MAKE-AND-BREAK CYCLES AT FULL LOAD.
 6. INSULATION RESISTANCE: 1,000 MEGA-OHM MIN.
 7. OPERATING TEMP.: -20°C to 55°C
 - ▲8. LAMP VOLTAGE: 12V DC
 9. ▲ DENOTES CRITICAL PARAMETER.
 10. 2002/05/EC (ROHS) COMPLIANT.
 11. PACKAGE: BOX/20 PIECES PER BOX
 - ▲12. LAMP COLOR: RED LED



PARTS LIST			
ITEM	QTY	PART NUMBER	DESCRIPTION
1	1	F040034	D16OAS22
2	1	F050420	5000420 12V DC LED (RED)
3	1	F050304	5000304 (TRANSPARENT) RED LENS



TITLE		D16OAS22JREDRED	
REV	PCR NO	DESCRIPTION	
A	17551	RELEASED FOR PRODUCTION	8/13/07
REV	PCR NO	DATE	BY
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED			
SCALE	1.5:1	DATE	1/10/2011
DR	BF	DWG	XF0835P
REV			A