


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
HM	00		Z	REV PER ECO-12-012918	09JUL2012	JM	JG

D

C

B

A



- 1 DIMENSIONS ARE MAXIMUM UNLESS OTHERWISE SPECIFIED.
- 2 MATERIAL: HOUSING—POLYCARBONATE,CLEAR. TERMINAL—0.36[.014] THICK PHOSPHOR BRONZE PLATED WITH 1.27 μ m[.000050] THICK GOLD IN LOCALIZED GOLD PLATE AREA, OVER 2.54 μ m[.000100] THICK NICKEL UNDERPLATE.
3. PLUG WILL ACCEPT 26 OR 28 AWG STRANDED WIRE HAVING A MAXIMUM INSULATION DIAMETER OF 0.99[.039] AND A MAXIMUM DIAMETER ROUND CABLE JACKET OF 2.54 [.100] OR OVAL CABLE JACKET OF 2.29 x 4.83[.090 x .190] MAXIMUM.
- 4 TERMINATED DIMENSION 6.15[.242] MAXIMUM.
- 5 10 ASSEMBLIES PER PACKAGE.
- 6 10,000 ASSEMBLIES PER PACKAGE.
- 7 1000 ASSEMBLIES PER PACKAGE.
- 8 100 ASSEMBLIES PER PACKAGE.
- 10 REELED PRODUCT ON STRIP DOES NOT HAVE VOID CORING ILLUSTRATED ON THIS DRAWING.

SUPERSEDED BY 5-641335-7	5	6-641335-3
	8	5-641335-3
	7	5-641335-2
	6	5-641335-1
OBSOLETE	REELED 10	641335-1
	PACKAGED	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN YTP/UTA 9-1-93		 TE Connectivity							
		CHK C.WHITT 9-15-93									
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME MODULAR PLUG ASSEMBLY, 4 POSITION, LINE -							
		APVD J.TONEY 9-20-93									
		PRODUCT SPEC 108-1163									
		APPLICATION SPEC 114-6016		SIZE A2		CAGE CODE 00779		DRAWING NO C-641335		RESTRICTED TO -	
		MATERIAL - 		FINISH - 		CUSTOMER DRAWING		SCALE 4:1		SHEET 1 of 1	