

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0529862671

Status:

Obsolete

Description:

1.27mm (.050") Pitch Wire-to-Board Shielded Receptacle, Right Angle, Dual Row, with Insert Nut for Screw Locks, 26 Circuits

Replacement Part Number:

529862679

Documents:

[Drawing \(PDF\)](#)

General	
Product Family	I/O Connectors
Series	52986
Application	Wire-to-Board
Component Type	Receptacle
Product Name	Leaf Style Contact
Replacement Part Number	529862679
Type	N/A

Physical	
Circuits (Loaded)	26
Circuits (maximum)	26
Color - Resin	Black
Durability (mating cycles max)	500
Lock to Mating Part	Yes
Material - Plating Mating	Gold
Material - Plating Termination	Tin-Lead
Material - Resin	Polyester
Number of Rows	2
Orientation	Right Angle
PC Tail Length	3.18mm (.125")
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm (.063")
Packaging Type	Tray
Panel Mount	Yes
Pitch - Mating Interface	1.27mm (.050")
Pitch - Termination Interface	1.27mm (.050")
Plating min - Mating	0.305µm (12µ")
Plating min - Termination	1.016µm (40µ")
Polarized to Mating Part	Yes
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-55°C to +85°C
Termination Interface: Style	Through Hole
Wire Size AWG	N/A

Electrical	
Current - Maximum per Contact	1A
Shielded	Yes
Voltage - Maximum	250V

Material Info

Reference - Drawing Numbers	
Product Specification	PS-52986-001, PS-52986-018, RPS-52986-031
Sales Drawing	SD-52986-018

EU RoHS

China RoHS

Not RoHS Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

52986Series

Mates With

54306 , [Link:52316](#)

This document was generated on 05/09/2011

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION